

## CLI C 3-24 SDR SG

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm<sup>2</sup> to max. 70 mm<sup>2</sup>. The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

### General ordering data

|            |                                                                                          |
|------------|------------------------------------------------------------------------------------------|
| Version    | CableLine, Conductor and cable markers, 8 - 16 mm, 24 x 11 mm, To customer specification |
| Order No.  | <a href="#">1912770000</a>                                                               |
| Type       | CLI C 3-24 SDR SG                                                                        |
| GTIN (EAN) | 4032248542611                                                                            |
| Qty.       | 100 Stück                                                                                |

Erstellungs-Datum May 22, 2023 12:50:15 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## CLI C 3-24 SDR SG

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |       |                 |            |
|------------|-------|-----------------|------------|
| Depth      | 17 mm | Depth (inches)  | 0.669 inch |
| Height     | 24 mm | Height (inches) | 0.945 inch |
| Width      | 11 mm | Width (inches)  | 0.433 inch |
| Net weight | 3 g   |                 |            |

### Temperatures

|                             |       |
|-----------------------------|-------|
| Operating temperature range | 80 °C |
|-----------------------------|-------|

### General data

|                             |                           |                                   |                            |
|-----------------------------|---------------------------|-----------------------------------|----------------------------|
| Colour                      | To customer specification | Colour of printing                | black                      |
| Halogen                     | Yes                       | Material                          | PVC, soft, without Cadmium |
| Operating temperature range | 80 °C                     | Operating temperature range, max. | 80 °C                      |
| Orientation of print        | horizontal                | Printed characters                | To customer specification  |
| Printing                    | Custom printing           | Printing method                   | Ink jet technology         |
| Type of printing            | To customer specification | UL 94 flammability rating         | V-0                        |
| Version                     | Loop                      | Width                             | 11 mm                      |

### Conductor and cable markers

|                               |                    |                                  |                         |
|-------------------------------|--------------------|----------------------------------|-------------------------|
| Conductor O.D.                | 8 - 16 mm          | Conductor O.D., max.             | 16 mm                   |
| Conductor O.D., min.          | 8 mm               | Conductor cross-section, max.    | 70 mm <sup>2</sup>      |
| Conductor cross-section, min. | 16 mm <sup>2</sup> | Cross-section for connected wire | 16 - 70 mm <sup>2</sup> |
| Halogen                       | Yes                |                                  |                         |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                             |                                                                      |
|-----------------------------|----------------------------------------------------------------------|
| Engineering Data            | <a href="#">WSCAD, EPLAN</a>                                         |
| Product Change Notification | <a href="#">PCN CableLine_DE</a><br><a href="#">PCN CableLine_EN</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>                             |

**CLI C 3-24 SDR SG**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**



Similar to illustration