

## CLI M 2-33 SDR SG

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections.

Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm<sup>2</sup>
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

### General ordering data

Version	CableLine, Conductor and cable markers, 10 - 317 mm, 33 x 11.4 mm, yellow
Order No.	<a href="#">1912920000</a>
Type	CLI M 2-33 SDR SG
GTIN (EAN)	4032248542727
Qty.	100 Stück

Erstellungs-Datum May 22, 2023 12:53:10 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## CLI M 2-33 SDR SG

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	3 mm	Depth (inches)	0.118 inch
Height	33 mm	Height (inches)	1.299 inch
Width	11.4 mm	Width (inches)	0.449 inch
Net weight	0.87 g		

### Temperatures

Operating temperature range	-30...80 °C
-----------------------------	-------------

### General data

Colour	yellow	Colour of printing	black
Halogen	Yes	Material	PVC, soft, without Cadmium
Number of markers per combination	1 Component part = Conductor and cable markers	Operating temperature range	-30...80 °C
Operating temperature range, max.	80 °C	Operating temperature range, min.	-30 °C
Printed characters	To customer specification	Printing	Custom printing
Printing method	Ink jet technology	Type of printing	To customer specification
UL 94 flammability rating	V-0	Version	Loop
Width	11.4 mm		

### Conductor and cable markers

Conductor O.D.	10 - 317 mm	Conductor O.D., max.	317 mm
Conductor O.D., min.	10 mm	Conductor cross-section, max.	500 mm <sup>2</sup>
Conductor cross-section, min.	16 mm <sup>2</sup>	Cross-section for connected wire	16 - 500 mm <sup>2</sup>
Halogen	Yes		

### Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">WSCAD, EPLAN</a>
Product Change Notification	<a href="#">PCN CableLine_DE</a> <a href="#">PCN CableLine_EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**CLI M 2-33 SDR SG**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**



Similar to illustration