

**SF 0/12 MC NE BL V2**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



Similar to illustration



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

**Advantages:**

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm<sup>2</sup>
- Markers in proven MultiCard format

**General ordering data**

Version	SlimFix, Conductor and cable markers, 1.2 - 1.6 mm, 12 x 3.2 mm, blue
Order No.	<a href="#">1919220000</a>
Type	SF 0/12 MC NE BL V2
GTIN (EAN)	4032248555611
Qty.	400 Stück
Alternative product	<a href="#">1919250000</a>
compatible printer	<a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a>

## SF 0/12 MC NE BL V2

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	3.2 mm	Depth (inches)	0.126 inch
Height	12 mm	Height (inches)	0.472 inch
Width	3.2 mm	Width (inches)	0.126 inch
Net weight	0.245 g		

### Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

### General data

Colour	blue	Halogen	No
Material	Polyamide 66	Material colour according to resistance code	6
Number of markers per combination	1 MultiCard = Conductor and cable markers	Operating temperature range	-40...100 °C
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Recommended industries	Transportation, Machinery	Size of labelling field	12 x 3.2 mm
Type of printing	neutral	UL 94 flammability rating	V-2
Width	3.2 mm		

### Conductor and cable markers

Conductor O.D.	1.2 - 1.6 mm	Conductor O.D., max.	1.6 mm
Conductor O.D., min.	1.2 mm	Conductor cross-section, max.	0.5 mm <sup>2</sup>
Conductor cross-section, min.	0.25 mm <sup>2</sup>	Cross-section for connected wire	0.25 - 0.5 mm <sup>2</sup>
Halogen	No		

### Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Datenblatt**

**SF 0/12 MC NE BL V2**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

