

THM WO 51/36 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 4 - 7.6 mm, 50.8 x 36 mm, white
Order No.	1934190000
Type	THM WO 51/36 WS
GTIN (EAN)	4032248590322
Qty.	1 Stück
compatible printer	2599430000 2599440000

Erstellungs-Datum May 22, 2023 1:07:57 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

THM WO 51/36 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	50.8 mm	Height (inches)	2 inch
Width	36 mm	Width (inches)	1.417 inch
Net weight	0.334 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

General data

Adhesive	Polyacrylate adhesive	Approval acc. to UL 969	Yes
Colour	white	Halogen	No
Material	Polyester film	Material colour according to resistance code	9
Number of markers per combination	1 Label reel = Conductor and cable markers	Number per roll	1,000 ST
Operating temperature range	-40...150 °C	Operating temperature range, max.	150 °C
Operating temperature range, min.	-40 °C	Size of labelling field	12.7 x 50.8 mm
Type of printing	neutral	UL 94 flammability rating	V-0
Version	Self-adhesive	Width	36 mm

Conductor and cable markers

Conductor O.D.	4 - 7.6 mm	Conductor O.D., max.	7.6 mm
Conductor O.D., min.	4 mm	Conductor cross-section, max.	400 mm ²
Conductor cross-section, min.	0.75 mm ²	Cross-section for connected wire	0.75 - 400 mm ²
Halogen	No	Text field height	12.7 mm
Text field width	50.8 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S, EPLAN
Catalogues	Catalogues in PDF-format

