

SF 2/12 MC SDR V2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format



General ordering data

Version	SlimFix, Conductor and cable markers, 2.2 - 2.9 mm, 12 x 3.6 mm, To customer specification
Order No.	191950000
Type	SF 2/12 MC SDR V2
GTIN (EAN)	4032248555796
Qty.	80 Stück
compatible printer	2715590000 2438520000 2438510000

SF 2/12 MC SDR V2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	3.65 mm	Depth (inches)	0.144 inch
Height	12 mm	Height (inches)	0.472 inch
Width	3.6 mm	Width (inches)	0.142 inch
Net weight	0.175 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

General data

Advice label	Colour based on customer requirements (Please send M-Print PRO file)	Colour	To customer specification
Colour of printing	black	Halogen	No
Material	Polyamide 66	Number of markers per combination	1 MultiCard = Conductor and cable markers
Operating temperature range	-40...100 °C	Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C	Orientation of print	horizontal
Printed characters	Based on customer requirements (Please send M-Print PRO file)	Printing method	MC Laser
Size of labelling field	12 x 3.6 mm	Type of printing	To customer specification
UL 94 flammability rating	V-2	Width	3.6 mm

Conductor and cable markers

Conductor O.D.	2.2 - 2.9 mm	Conductor O.D., max.	2.9 mm
Conductor O.D., min.	2.2 mm	Conductor cross-section, max.	1.5 mm ²
Conductor cross-section, min.	0.75 mm ²	Cross-section for connected wire	0.75 - 1.5 mm ²
Halogen	No		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format