

SF 5/12 MC NE GE V2


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration



SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm²
- Markers in proven MultiCard format

General ordering data

| | |
|--------------------|--|
| Version | SlimFix, Conductor and cable markers, 4.7 - 7.4 mm, 12 x 7.4 mm, yellow |
| Order No. | 1919620000 |
| Type | SF 5/12 MC NE GE V2 |
| GTIN (EAN) | 4032248556045 |
| Qty. | 160 Stück |
| compatible printer | 2715590000 2438520000 2438510000 |

SF 5/12 MC NE GE V2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 8 mm | Depth (inches) | 0.315 inch |
| Height | 12 mm | Height (inches) | 0.472 inch |
| Width | 7.4 mm | Width (inches) | 0.291 inch |
| Net weight | 0.769 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

General data

| | | | |
|-----------------------------------|---|--|--------------|
| Colour | yellow | Halogen | No |
| Material | Polyamide 66 | Material colour according to resistance code | 4 |
| Number of markers per combination | 1 MultiCard = Conductor and cable markers | Operating temperature range | -40...100 °C |
| Operating temperature range, max. | 100 °C | Operating temperature range, min. | -40 °C |
| Recommended industries | Transportation, Machinery | Size of labelling field | 12 x 7.4 mm |
| Type of printing | neutral | UL 94 flammability rating | V-2 |
| Width | 7.4 mm | | |

Conductor and cable markers

| | | | |
|-------------------------------|-------------------|----------------------------------|-----------------------|
| Conductor O.D. | 4.7 - 7.4 mm | Conductor O.D., max. | 7.4 mm |
| Conductor O.D., min. | 4.7 mm | Conductor cross-section, max. | 6 mm ² |
| Conductor cross-section, min. | 4 mm ² | Cross-section for connected wire | 4 - 6 mm ² |
| Halogen | No | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, Zuken E3.S, EPLAN |
| Catalogues | Catalogues in PDF-format |

Datenblatt

SF 5/12 MC NE GE V2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

