

## SF 5/12 MC SDR V2

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

SlimFix are conductor and cable markers with a space-saving design. The markers can be fitted even after the conductor has been installed. They consist of halogen-free material and comply with flammability rating V0/V2. SlimFix is an acknowledged and accredited marker type for traffic engineering applications. The SF tool allows easy installation, even in case of small markers.

### Advantages:

- Halogen-free material
- Flammability rating V0/V2
- Approved and accredited markers for traffic engineering applications, etc.
- Has to be fixed with cable ties if the conductor cross-section is larger than 16.0 mm<sup>2</sup>
- Markers in proven MultiCard format

### General ordering data

|                    |  |
|--------------------|--|
| Version            | SlimFix, Conductor and cable markers, 4.7 - 7.4 mm, 12 x 7.4 mm, To customer specification |
| Order No.          | <a href="#">1919660000</a>   |
| Type               | SF 5/12 MC SDR V2  |
| GTIN (EAN)         | 4032248556083  |
| Qty.               | 32 Stück   |
| compatible printer | <a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a>           |

## SF 5/12 MC SDR V2

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 8 mm    | Depth (inches)  | 0.315 inch |
| Height     | 12 mm   | Height (inches) | 0.472 inch |
| Width      | 7.4 mm  | Width (inches)  | 0.291 inch |
| Net weight | 0.469 g |                 |            |

### Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

### General data

|                                   |  |                                   |   |
|-----------------------------------|--|-----------------------------------|---|
| Advice label                      | Colour based on customer requirements (Please send M-Print PRO file) | Colour                            | To customer specification                 |
| Colour of printing                | black  | Halogen                           | No  |
| Material                          | Polyamide 66   | Number of markers per combination | 1 MultiCard = Conductor and cable markers |
| Operating temperature range       | -40...100 °C   | Operating temperature range, max. | 100 °C                                    |
| Operating temperature range, min. | -40 °C   | Orientation of print              | horizontal                                |
| Printed characters                | Based on customer requirements (Please send M-Print PRO file)        | Printing method                   | MC Laser                                  |
| Size of labelling field           | 12 x 7.4 mm  | Type of printing                  | To customer specification                 |
| UL 94 flammability rating         | V-2  | Width                             | 7.4 mm                                    |

### Conductor and cable markers

|                               |                   |                                  |                       |
|-------------------------------|-------------------|----------------------------------|-----------------------|
| Conductor O.D.                | 4.7 - 7.4 mm      | Conductor O.D., max.             | 7.4 mm                |
| Conductor O.D., min.          | 4.7 mm            | Conductor cross-section, max.    | 6 mm <sup>2</sup>     |
| Conductor cross-section, min. | 4 mm <sup>2</sup> | Cross-section for connected wire | 4 - 6 mm <sup>2</sup> |
| Halogen                       | No                |                                  |                       |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">WSCAD, EPLAN</a>             |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |