

HDC 48B SDLU 2M50G

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Version	HDC enclosures, Size: 12, Protection degree: IP65 (in plugged condition), Base housing, End-locking clamp, lower side, Standard, with cover, Size of cable entries: M 50
Order No.	1983510000
Type	HDC 48B SDLU 2M50G
GTIN (EAN)	4032248687770
Qty.	1 pc(s).

HDC 48B SDLU 2M50G

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

Depth	143 mm	Depth (inches)	5.63 inch
Height	120 mm	Height (inches)	4.724 inch
Width	166.2 mm	Width (inches)	6.543 inch
Mounting dimension - height	106 mm	Mounting dimension - width	111 mm
Net weight	1,445 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Dimensions

Cable entry	w. thread	Height of base B1	10 mm
Height of housing B	120 mm	Hole pitch length A2	111 mm
Total length housing	132 mm	Width base C1	120 mm
Width housing C	90 mm		

General data

EMC housings	No	Housing main material	diecast aluminium
Material of locking element	Stainless steel, rust-proof	Protection class note	Protection class with secured cover: IP 65
Protection degree	IP65 (in plugged condition)	Surface finish	Powder coating
Tightening torque	1.2 Nm		

Version

BG	12	Cable entry	w. thread
Clamp version	End-locking clamp	Colour (RAL)	RAL 7035
Cover	with cover	Design	Standard
Design of cover	with cover	Design of housing	Base housing
Design of locking system	End-locking clamp, lower side	Internal thread	M 50
Number of cable entry on top	0	Number of cable entry sideways	1
Sealing	NBR	Size	12
Size of cable entries	M 50	Suitable for ModuPlug®	Yes
Tightening torque	1.2 Nm	Top part/bottom part/lid	lower part
Type	Base housing		

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ECLASS 9.0	27-44-02-02
ECLASS 9.1	27-44-02-02	ECLASS 10.0	27-44-02-02
ECLASS 11.0	27-44-02-02	ECLASS 12.0	27-44-02-02

Substance	Acetone
Chemical resistance	Conditionally resistant
Substance	Drilling oil
Chemical resistance	Resistant
Substance	Diesel
Chemical resistance	Resistant

Creation date March 9, 2023 2:22:13 PM CET

HDC 48B SDLU 2M50G

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Substance	Ethyl alcohol
Chemical resistance	Resistant
Substance	Transmission oil
Chemical resistance	Resistant
Substance	Hydraulic oil
Chemical resistance	Resistant
Substance	Coolant
Chemical resistance	Resistant
Substance	Petroleum benzine
Chemical resistance	Resistant
Substance	Sweat
Chemical resistance	Resistant
Substance	Premium gasoline
Chemical resistance	Conditionally resistant
Substance	Water
Chemical resistance	Resistant
Substance	UV
Chemical resistance	Unstable
Substance	Ozone
Chemical resistance	Unstable

Environmental Product Compliance

REACH SVHC

Lead 7439-92-1

SCIP

d447edfa-0214-4f34-b5ba-82eae491b46a

Chemical resistance

de.myview.objectmodel.impl.BlockImpl@627d6844 de.myview.objectmodel.impl.BlockImpl@2f0eed70
 de.myview.objectmodel.impl.BlockImpl@19c7a5d8 de.myview.objectmodel.impl.BlockImpl@38a5fc1f
 de.myview.objectmodel.impl.BlockImpl@31138c07 de.myview.objectmodel.impl.BlockImpl@69ae9238
 de.myview.objectmodel.impl.BlockImpl@4de313b0 de.myview.objectmodel.impl.BlockImpl@5ab14b17
 de.myview.objectmodel.impl.BlockImpl@77ef97f2 de.myview.objectmodel.impl.BlockImpl@6acde465
 de.myview.objectmodel.impl.BlockImpl@3f66141f de.myview.objectmodel.impl.BlockImpl@6fdf0917
 de.myview.objectmodel.impl.BlockImpl@64045319

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data

[CAD data – STEP](#)

Product Change Notification

[20220214 Technical change to HDC housings](#)
[20220214 Technische Änderung bei HDC-Gehäusen](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

Creation date March 9, 2023 2:22:13 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

HDC 48B SDLU 2M50G**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Drawings