

PAC-HD62F-HD62F-V0-1M5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm² or 0.25 mm².
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

General ordering data

| | |
|------------|----------------------------|
| Version | |
| Order No. | 1988930015 |
| Type | PAC-HD62F-HD62F-V0-1M5 |
| GTIN (EAN) | 4032248340842 |
| Qty. | 1 Stück |

PAC-HD62F-HD62F-V0-1M5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 471 g

Temperatures

| | | | |
|-----------------------------|-------------|-----------------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
| Operating temperature, min. | -10 °C | Operating temperature, max. | 50 °C |

General Data

| | | | |
|--------------------|----------------------|-----------------------|---------------------|
| Cable | Cable LiYCY | Cable length | 1.5 m |
| Connector PLC side | SUB-D HD female 62P | Interface connector | SUB-D HD female 62P |
| Material | PVC | Number of poles, min. | 62 poles |
| Outer diameter | 12,5 ± 2 mm | Suitable for | Analogue signals |
| Wire cross-section | 0.14 mm ² | | |

Electrical Data

| | | | |
|---|------------|-----------------------|---------------------|
| Capacity wire / shield | 300 pF/m | Capacity wire / wires | 300 pF/m |
| High voltage test | 1 KV/1s | Operating voltage | ≤ 60 V DC ≤ 25 V AC |
| Permissible current strength per path, max. | 1 A | Rated voltage | ≤ 60 Vdc ≤ 25 Vac |
| Resistance | ≤ 150 mΩ/m | Total current, max. | 3 A |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000237 | ETIM 7.0 | EC000237 |
| ETIM 8.0 | EC000237 | ECLASS 9.0 | 27-24-22-20 |
| ECLASS 9.1 | 27-24-22-20 | ECLASS 10.0 | 27-24-22-20 |
| ECLASS 11.0 | 27-24-22-20 | ECLASS 12.0 | 27-24-22-20 |

Approvals

ROHS Conform

Downloads

Catalogues [Catalogues in PDF-format](#)