

THM WO 24.5/100 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 8 - 23 mm, 25.4 x 100 mm, white
Order No.	2004970000
Type	THM WO 24.5/100 WS
GTIN (EAN)	4050118415391
Qty.	2,000 Stück
compatible printer	2599430000 2599440000

Erstellungs-Datum May 22, 2023 1:13:56 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

THM WO 24.5/100 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	25.4 mm	Height (inches)	1 inch
Width	100 mm	Width (inches)	3.937 inch
Net weight	0.406 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

General data

Adhesive	Polyacrylate adhesive	Colour	white
Halogen	No	Material	Polyester film
Number of markers per combination	1 Label reel = Conductor and cable markers	Number per roll	2,000
Operating temperature range	-40...150 °C	Operating temperature range, max.	150 °C
Operating temperature range, min.	-40 °C	Size of labelling field	24.5 x 25 mm
Type of printing	neutral	UL 94 flammability rating	V-0
Width	100 mm		

Conductor and cable markers

Conductor O.D.	8 - 23 mm	Conductor O.D., max.	23 mm
Conductor O.D., min.	8 mm	Conductor cross-section, max.	120 mm ²
Conductor cross-section, min.	0.75 mm ²	Cross-section for connected wire	0.75 - 120 mm ²
Halogen	No	Text field height	25 mm
Text field width	24.5 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN
Catalogues	Catalogues in PDF-format