


HSS-HF 3/16 2.8-4.2/25Y

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

| | |
|--------------------|--|
| Version | Conductor and cable markers, 2.8 - 4.2 mm, 25.4 x 8.4 mm, yellow |
| Order No. | 1961980000 |
| Type | HSS-HF 3/16 2.8-4.2/25Y |
| GTIN (EAN) | 4032248642670 |
| Qty. | 8,000 Stück |
| compatible printer | 2599430000 2599440000 |

Erstellungs-Datum May 22, 2023 1:10:18 PM CEST

HSS-HF 3/16 2.8-4.2/25Y

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 0.77 mm | Depth (inches) | 0.03 inch |
| Height | 25.4 mm | Height (inches) | 1 inch |
| Width | 8.4 mm | Width (inches) | 0.331 inch |
| Net weight | 0.336 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -55...105 °C |
|-----------------------------|--------------|

General data

| | | | |
|-----------------------------------|--------------|--|----------------|
| Colour | yellow | Halogen | No |
| Material | Polyolefine | Material colour according to resistance code | 4 |
| Operating temperature range | -55...105 °C | Operating temperature range, max. | 105 °C |
| Operating temperature range, min. | -55 °C | Recommended industries | Transportation |
| Type of printing | neutral | Width | 8.4 mm |

Conductor and cable markers

| | | | |
|-----------------------------------|---------------------|----------------------------------|-------------------------|
| Conductor O.D. | 2.8 - 4.2 mm | Conductor O.D., max. | 4.2 mm |
| Conductor O.D., min. | 2.8 mm | Conductor cross-section, max. | 4 mm ² |
| Conductor cross-section, min. | 1.5 mm ² | Cross-section for connected wire | 1.5 - 4 mm ² |
| Halogen | No | Rate of shrinkage | 2:1 |
| Recommended shrinking temperature | 90 °C | Text field height | 8.05 mm |
| Text field width | 25.4 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | NFX 70-100-1 2006 + NF X 70-100-2 2006 BS EN ISO 4589-2 1999 EN 45545-2:2020 |
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, Zuken E3.S, EPLAN |
| Catalogues | Catalogues in PDF-format |

HSS-HF 3/16 2.8-4.2/25Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Zeichnungen

www.weidmueller.com



Bestellhilfe

HSS-HF 1/8" 1,2-2,8 / 50 Y

- Y = Gelb (W=Weiß)
- 50,8 mm Hüslenlänge (oder 25,4 mm)
- geeigneter Leiterdurchmesser 1,2 - 2,8mm
- Max. Außendurchmesser 1/8" (bzw. 3,2 mm)
- HF = Halogenfrei nach VDE 0472-615
- HSS = Heat Shrinkable Sleeve (wärmeschrumpfender Schlauch)