

## WM 2/6 3.5-5.0 MM WS

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



### Un-detachable: WM

Our closed, un-detachable markers are mounted without the need for additional tools. The cable is simply threaded through the openings at both ends before the cables are fixed in position. The inherent tension of the material fixes the marker in place. WM markers are available in four sizes for conductor cross-sections from 0.25mm<sup>2</sup> to 16mm<sup>2</sup>. Each size comes in three label lengths and two colours. This provides you with just the right assortment for carrying out everyday labelling of conductors in a cabinet.

### Your benefits with MultiMark

- Compact, practice-oriented range of products
- Quickly printed and assembled
- Reliable identification of your connections
- Excellent material properties

### General ordering data

Version	WM, Conductor and cable markers, 3.5 - 5 mm, 17 x 6.4 mm, white
Order No.	<a href="#">2006370000</a>
Type	WM 2/6 3.5-5.0 MM WS
GTIN (EAN)	4050118390186
Qty.	2,000 Stück
compatible printer	<a href="#">2599430000</a> <a href="#">2599440000</a>

## WM 2/6 3.5-5.0 MM WS

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	0.5 mm	Depth (inches)	0.02 inch
Height	17 mm	Height (inches)	0.669 inch
Width	6.4 mm	Width (inches)	0.252 inch
Net weight	0.112 g		

### Temperatures

Operating temperature range	-40...150 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	150 °C	Continuous operating temp., min.	-40
Continuous operating temp., max.	150		

### General data

Colour	white	Halogen	No
Material	Polyester	Operating temperature range	-40...150 °C
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
Size of labelling field	7 x 6.4 mm	UL 94 flammability rating	HB
Version	halogen-free	Width	6.4 mm

### Conductor and cable markers

Conductor O.D.	3.5 - 5 mm	Conductor O.D., max.	5 mm
Conductor O.D., min.	3.5 mm	Conductor cross-section, max.	4 mm <sup>2</sup>
Conductor cross-section, min.	2.5 mm <sup>2</sup>	Cross-section for connected wire	2.5 - 4 mm <sup>2</sup>
Halogen	No	Text field height	6.4 mm
Text field width	7 mm		

### Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**WM 2/6 3.5-5.0 MM WS**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

