

BKP-16DO-SDV541-V0-S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The digital output interfaces via relay are used to isolate the field sensors from the card and/or to adapt the operation of the said elements to the voltage required by the DCS. The interfaces also support additional characteristics that provide many benefits such as:

- **Redundancy: the interfaces have 2 50-pole (AKB) connectors for redundancy purposes.**
- **Many of the interfaces activate a relay to indicate if one of the two possible power sources has dropped below a value of approximately 12 V**
- **The cards can be mounted via tension clamp or screw connection.**
- **The input sensors can be connected in two ways: supplied with power directly from the card or directly from the field.**

General ordering data

Version	2 x AKB (50P)
Order No.	2461730000
Type	BKP-16DO-SDV541-V0-S
GTIN (EAN)	4050118476965
Qty.	1 pc(s).

BKP-16DO-SDV541-V0-S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	125 mm	Depth (inches)	4.921 inch
Height	168 mm	Height (inches)	6.614 inch
Width	376 mm	Width (inches)	14.803 inch
Net weight	3,875 g		

Temperatures

Storage temperature	-40...85 °C	Operating temperature	-25...50 °C
Operating temperature, min.	-25 °C	Operating temperature, max.	50 °C

General data

Power supply fuse	2 A
-------------------	-----

Connection data

Connection on control side	2 x AKB (50P)	Connection supply	LP 5.08mm
Number of poles (control side)	50-pole plug		

Ratings data output

Relay type	SIL3
------------	------

Insulation coordinates (EN50178)

Rated input insulation voltage	50 V AC / 70 V DC	Rated output insulation voltage	< 300 V AC
Overvoltage category input/input	III	Overvoltage category input/output	III
Overvoltage category output/output	III	Pollution severity level	2
Pulse voltage test (1,2/50µs)	6 kV	Insulation test voltage	1.2 kVAC
Clearance input/output	≥ 5.5 mm	Clearance input/input	≥ 0.3 mm
Clearance output/output	≥ 5.5 mm		

Connection field

Clamping range, max.	2.5 mm ²	Clamping range, min.	0.13 mm ²
Flexible with sleeve, max.	2.5 mm ²	Flexible with sleeve, min.	0.2 mm ²
Flexible, max. H05(07) V-K	2.5 mm ²	Flexible, min. H05(07) V-K	0.2 mm ²
Max. wire cross-section, AWG	AWG 14	Min. wire cross-section, AWG	AWG 26
Solid, max. H05(07) V-U	2.5 mm ²	Solid, min. H05(07) V-U	0.2 mm ²
Stripping length	6 mm	Type of connection	Screw connection

Supply connection

Type of connection	Screw connection	Clamping range, min.	0.13 mm ²
Clamping range, max.	6 mm ²	Solid, min. H05(07) V-U	0.5 mm ²
Solid, max. H05(07) V-U	6 mm ²	Flexible, min. H05(07) V-K	0.5 mm ²
Flexible, max. H05(07) V-K	4 mm ²	Flexible with sleeve, max.	2.5 mm ²
Flexible with sleeve, min.	2.5 mm ²	Ferrule with plastic collar, max.	0.5 mm ²
Wire cross-section, min. AWG	AWG 12	Wire cross-section, max. AWG	AWG 26
Tightening torque, min.	0.5 Nm	Tightening torque, max.	0.6 Nm
Stripping length	6 mm		

BKP-16DO-SDV541-V0-S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Classifications

ETIM 6.0	EC002780	ETIM 7.0	EC002780
ETIM 8.0	EC002780	ECLASS 9.0	27-14-11-52
ECLASS 9.1	27-24-22-16	ECLASS 10.0	27-14-11-52
ECLASS 11.0	27-14-11-52	ECLASS 12.0	27-14-11-52

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Approvals

Approvals



Downloads

Approval/Certificate/Document of
Conformity [Declaration of Conformity](#)

Catalogues [Catalogues in PDF-format](#)

BKP-16DO-SDV541-V0-S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Drawings

