

**AEP MC 2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image****Power distribution**

You safely and efficiently distribute electricity to the power consumers with our W-Series feed-through terminal blocks and our optimised WPD phase distribution blocks.

**General ordering data**

Version	A-series, End plate
Order No.	<a href="#">2433820000</a>
Type	AEP MC 2.5
GTIN (EAN)	4050118444278
Qty.	25 pc(s).

Creation date March 9, 2023 8:19:53 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

## AEP MC 2.5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	87.7 mm	Depth (inches)	3.453 inch
Height	106.8 mm	Height (inches)	4.205 inch
Width	1 mm	Width (inches)	0.039 inch
Net weight	7.1 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

## Material data

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

## System specifications

Version	End plate
---------	-----------

## Additional technical data

Snap-on	Yes	With snap-in pegs	Yes
---------	-----	-------------------	-----

## Classifications

ETIM 6.0	EC000886	ETIM 7.0	EC000886
ETIM 8.0	EC000886	ECLASS 9.1	27-14-11-33
ECLASS 10.0	27-14-11-33	ECLASS 11.0	27-14-11-33
ECLASS 12.0	27-14-11-33		

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>