

## VG M40 EMV-4 MS 22-32

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



#### Produktabbildung

The increasing sensitivity of electronic components and the increasing electromagnetic interference frequencies require cable glands to play an important role in the shielding concept of a system. This type of EMC cable glands are made for shielding against interference frequencies, with a 360° screening connection. A Finger-locking seal provides superior cable retention & strain relief, next to it, the cable gland meets the mechanical requirements of EN 62444. Due to the patented design a very easy and fast assembly will be possible.

#### General ordering data

Version	VG EMV GEN 4 (EMC cable gland with clamping cage), Cable glands, straight, M 40, 9, OD min. 22 - OD max. 32 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), IP69K, Brass, nickel-plated
Order No.	<a href="#">2435190000</a>
Type	VG M40 EMV-4 MS 22-32
GTIN (EAN)	4050118446944
Qty.	5 pc(s).

Creation date March 9, 2023 8:22:03 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

## VG M40 EMV-4 MS 22-32

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Length	69.5 mm	Length (inches)	2.736 inch
Net weight	0.278 g		

### Temperatures

Operating temperature	-40 °C...100 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	100 °C		

### Certificate numbers cable gland

Approval conditions	DNV, UL, cULus	Certificate no. cable gland (GERMILLOYD)	E-14047
Certificate no. cable gland (UL)	E199260	Certificate no. cable gland (cULus)	E199260

### General information

AF size	50 mm	AF size 1	50 mm
AF size 2	50 mm	Cable glands	metric, M 40
Clamp insert	Polyamide	External thread	M 40
Halogen	Yes	Length of thread	9 mm
Material	Brass, nickel-plated	O-Ring	NBR
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Outer cable diameter, max.	32 mm	Outer cable diameter, min.	22 mm
Pitch of thread	1.5 mm	Protection degree	IP66, IP68 - 5 bar (30 min.), IP69K
Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.), IP69K	Seal insert	CR
Shield diameter, max.	27 mm	Shield diameter, min.	18 mm
Tightening torque	12 Nm	Torque for cap nut, max.	43 Nm
Torque for cap nut, min.	41 Nm	Torque for connecting adapter, max.	12.5 Nm
Torque for connecting adapter, min.	11.5 Nm		

### Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32	ECLASS 12.0	27-14-08-01

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

### Approvals

ROHS	Conform
------	---------

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">EU Declaration of Conformity - EMC brass nickel plated cable gland - DE PS2480 210608 004ISS00</a>
Engineering Data	<a href="#">CAD data - STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

Creation date March 9, 2023 8:22:03 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.