

**HS 0.8-2.4/50 MM Y****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

|                    |  |
|--------------------|--|
| Version            | Conductor and cable markers, 0.8 - 2.4 mm, 50.8 x 4.2 mm, yellow |
| Order No.          | <a href="#">243750000</a>  |
| Type               | HS 0.8-2.4/50 MM Y   |
| GTIN (EAN)         | 4050118461008  |
| Qty.               | 1,000 Stück  |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a>            |

## HS 0.8-2.4/50 MM Y

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.77 mm | Depth (inches)  | 0.03 inch  |
| Height     | 50.8 mm | Height (inches) | 2 inch     |
| Width      | 4.2 mm  | Width (inches)  | 0.165 inch |
| Net weight | 0.502 g |                 |            |

### Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -55...135 °C |
|-----------------------------|--------------|

### General data

|                                   |              |                                   |   |
|-----------------------------------|--------------|-----------------------------------|---|
| Colour                            | yellow       | Halogen                           | Yes   |
| Material                          | Polyolefine  | Number per roll                   | 1,000   |
| Operating temperature range       | -55...135 °C | Operating temperature range, max. | 135 °C  |
| Operating temperature range, min. | -55 °C       | Recommended industries            | Plant manufacture, Energy, Device manufacturer, Machinery |
| Width                             | 4.2 mm       |                                   |   |

### Conductor and cable markers

|                                   |                      |                                  |                            |
|-----------------------------------|----------------------|----------------------------------|----------------------------|
| Conductor O.D.                    | 0.8 - 2.4 mm         | Conductor O.D., max.             | 2.4 mm                     |
| Conductor O.D., min.              | 0.8 mm               | Conductor cross-section, max.    | 0.5 mm <sup>2</sup>        |
| Conductor cross-section, min.     | 0.25 mm <sup>2</sup> | Cross-section for connected wire | 0.25 - 0.5 mm <sup>2</sup> |
| Halogen                           | Yes                  | Rate of shrinkage                | 3:1                        |
| Recommended shrinking temperature | 90 °C                |                                  |                            |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ECLASS 9.0  | 27-40-04-01 |
| ECLASS 9.1  | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">EPLAN</a>                    |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

**Datenblatt**

**HS 0.8-2.4/50 MM Y**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

