

VPU PV I+II O 1000 E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



Similar to illustration



General ordering data

Version	Surge voltage arrester, Low voltage, Accessories, Surge protection I / II, Spare arrester
Order No.	2530530000
Type	VPU PV I+II O 1000 E
GTIN (EAN)	4050118540741
Qty.	9 Stück

VPU PV I+II 0 1000 E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	63 mm	Depth (inches)	2.48 inch
Height	45 mm	Height (inches)	1.772 inch
Width	18 mm	Width (inches)	0.709 inch
Net weight	9.444 g		

Temperatures

Storage temperature	85 °C	Operating temperature	-40 °C...85 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	85 °C
Humidity	5 - 95% rel. humidity		

General data

Colour	orange	Operating altitude	≤ 4000 m
Optical function display	green = OK; red = arrester is defective - replace	Protection degree	IP20
UL 94 flammability rating	V-0	Version	Surge protection I / II, Spare arrester

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

Photovoltaic technical data

Discharge current I_n (8/20 μ s)	20 kA	Discharge current, max. (8/20 μ s)	40 kA
Lightning test current I_{imp} (10/350 μ s)	5 kA	Operating height in the grounded PV system	≤ 2000 m
PV system voltage, max. U_{cpv}	1,100 V	Protection level U_p (+/-, -/PE, +/-PE)	≤ 3.8 kV
Requirements class	Type I/II	Short-circuit current I_{SCPV}	11,000 A
Standards	EN 61643-31, EN 50539-11	Total discharge current I_{total} (8/20 μ s)	50 kA
Total discharge current I_{total} (10/350 μ s)	6.25 kA		

Rated data IEC / EN

Discharge current, max. (8/20 μ s)	40 kA	Leakage current at U_n	30 μ A
Lightning test current I_{imp} (10/350 μ s)	5 kA	Number of poles	1
Response time	≤ 25 ns	SPD type	T1, T2
Standards	EN 61643-31, EN 50539-11	Voltage type	DC

Connection data

Type of connection	pluggable
--------------------	-----------

Guarantee

Time interval	5 years
---------------	---------

VPU PV I+II 0 1000 E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ECLASS 9.0	27-13-08-05
ECLASS 9.1	27-13-08-05	ECLASS 10.0	27-13-08-05
ECLASS 11.0	27-13-08-05	ECLASS 12.0	27-17-90-90

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	EAC_VPU_SERIES CE_VPU_PV
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

Zeichnungen

Electric symbol

