


VPU PV I+II 3 1000

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Product image



Similar to illustration

General ordering data

Version	Surge voltage arrester, Low voltage, Surge protection I / II
Order No.	2530610000
Type	VPU PV I+II 3 1000
GTIN (EAN)	4050118540826
Qty.	1 Stück
Replacement parts	2530600000 2534300000

Erstellungs-Datum May 22, 2023 4:18:23 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

VPU PV I+II 3 1000

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	86 mm	Depth (inches)	3.386 inch
Height	96 mm	Height (inches)	3.78 inch
Width	54 mm	Width (inches)	2.126 inch
Mounting dimension - height	85 mm	Net weight	470 g

Temperatures

Storage temperature	85 °C	Operating temperature	-40 °C...85 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	85 °C
Humidity	5 - 95% rel. humidity		

Rated data UL

Ambient temperature (operational), max. 85 °C		Rated Voltage U_N	1,100 V
SCCR	50 kA	I_n	20 kA
Category	SPD TYPE 1CA	Ambient temperature (operational), min. -40 °C	
Certificate No. (cURus)	E354261	VPR (DC+/DC-)	2,500 V
Voltage type	DC		

General data

Colour	black, orange	Design	Installation housing; 3TE, Insta IP 20
Operating altitude	≤ 4000 m	Optical function display	green = OK; red = arrester is defective - replace
Protection degree	IP20	Rail	TS 35
UL 94 flammability rating	V-0	Version	Surge protection I / II

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

Photovoltaic technical data

Discharge current I_n (8/20 μs)	20 kA	Discharge current, max. (8/20 μs)	40 kA
Lightning test current I_{imp} (10/350 μs)	6.25 kA	Operating height in the grounded PV system	≤ 2000 m
Operating height in ungrounded PV system	< 4,000 m, see operating instructions	PV system voltage, max. U_{cpv}	1,100 V
Protection level U_p (+/-, -/PE, +/-PE)	≤ 3.8 kV	Requirements class	Type I/II
Short-circuit current I_{SCPv}	11,000 A	Standards	EN 61643-31, EN 50539-11, UL 1449
Total discharge current I_{total} (8/20μs)	50 kA	Total discharge current I_{total} (10/350μs)	12.5 kA

Rated data IEC / EN

Discharge current, max. (8/20 μs)	40 kA	Leakage current at U_n	30 μA
Lightning test current I_{imp} (10/350 μs)	6.25 kA	Number of poles	3
Rated voltage (DC)	1000 V	Response time	≤ 25 ns
SPD type	T1, T2	Signalling contact	No
Standards	EN 61643-31, EN 50539-11, UL 1449	Voltage type	DC

Erstellungs-Datum May 22, 2023 4:18:23 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

VPU PV I+II 3 1000

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Connection data

Stripping length	18 mm	Type of connection	Screw connection
Stripping length, rated connection	18 mm	Tightening torque, min.	2 Nm
Tightening torque, max.	4.5 Nm	Clamping range, rated connection	16 mm ²
Clamping range, min.	1.5 mm ²	Clamping range, max.	35 mm ²
Wire cross-section, solid, min.	1.5 mm ²	Wire cross-section, solid, max.	16 mm ²
Wire connection cross section, finely stranded, min.	1.5 mm ²	Wire connection cross section, finely stranded, max.	25 mm ²
Connection cross-section, stranded, min.	1.5 mm ²	Connection cross-section, stranded, max.	35 mm ²

Guarantee

Time interval	5 years
---------------	---------

Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ECLASS 9.0	27-13-08-05
ECLASS 9.1	27-13-08-05	ECLASS 10.0	27-13-08-05
ECLASS 11.0	27-13-08-05	ECLASS 12.0	27-17-90-90

Approvals

Approvals




ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E354261

Downloads

Approval/Certificate/Document of Conformity	EAC VPU SERIES CE VPU PV
Engineering Data	CAD data – STEP
Engineering Data	EPLAN
Tender specification	Ausschreibungstext DE Tenderspecification EN
User Documentation	Beipackzettel / Instruction sheet
Catalogues	Catalogues in PDF-format

Electric symbol



Circuit diagram