

VPU PV II O 1000

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



General ordering data

Version	Surge voltage arrester, Low voltage, Accessories, Spare arrester
Order No.	2530660000
Type	VPU PV II O 1000
GTIN (EAN)	4050118540871
Qty.	9 Stück

VPU PV II O 1000

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	63 mm	Depth (inches)	2.48 inch
Height	45 mm	Height (inches)	1.772 inch
Width	18 mm	Width (inches)	0.709 inch
Net weight	7.703 g		

Temperatures

Storage temperature	85 °C	Operating temperature	-40 °C...85 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	85 °C
Humidity	5 - 95% rel. humidity		

Rated data UL

Ambient temperature (operational), max. 85 °C		Rated Voltage U_N	550 V
SCCR	50 kA	I_n	20 kA
Category	SPD TYPE 1CA	Ambient temperature (operational), min. -40 °C	
Certificate No. (cURus)	E354261	VPR (DC+/DC-)	2,500 V
Voltage type	DC		

General data

Colour	orange	Operating altitude	≤ 4000 m
Optical function display	green = OK; red = arrester is defective - replace	Protection degree	IP20
UL 94 flammability rating	V-0	Version	Spare arrester

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

Photovoltaic technical data

Discharge current I_n (8/20 μs)	20 kA	Discharge current, max. (8/20 μs)	40 kA
Operating height in the grounded PV system	≤ 2000 m	PV system voltage, max. U_{cpv}	1,100 V
Protection level U_p (+/-, -/PE, +/-PE)	≤ 3.8 kV	Requirements class	Type II
Short-circuit current I_{SCPV}	11,000 A	Standards	EN 61643-31, EN 50539-11, UL 1449
Total discharge current I_{total} (8/20μs)	50 kA		

Rated data IEC / EN

Discharge current, max. (8/20 μs)	40 kA	Leakage current at U_n	30 μA
Number of poles	1	Response time	≤ 25 ns
SPD type	T2	Standards	EN 61643-31, EN 50539-11, UL 1449
Voltage type	DC		

Connection data

Type of connection	pluggable
--------------------	-----------

VPU PV II 0 1000

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Garantie

Time interval 5 years

Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ECLASS 9.0	27-13-08-05
ECLASS 9.1	27-13-08-05	ECLASS 10.0	27-13-08-05
ECLASS 11.0	27-13-08-05	ECLASS 12.0	27-17-90-90

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E354261

Downloads

Approval/Certificate/Document of Conformity	EAC VPU SERIES CE VPU PV
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

Zeichnungen

Electric symbol

