

IE-BSS-VAPM-24V

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



PushPull Power plug-in connector according to PROFINET specification

General ordering data

Version	Power connector, Flange, PROFINET, Set of flanges
Order No.	2493480000
Type	IE-BSS-VAPM-24V
GTIN (EAN)	4050118522143
Qty.	1 Stück

Erstellungs-Datum May 15, 2023 4:29:25 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

IE-BSS-VAPM-24V

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Width	46 mm	Width (inches)	1.811 inch
Length	66 mm	Length (inches)	2.598 inch
Net weight	54 g		

Temperatures

Operating temperature	-40 °C...70 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	70 °C		

General data

Colour	Silver grey	Connection 1	PushPull Power
Connection 2	Tension clamp	Contact material	Copper alloy
Contact surface	Gold over nickel	Housing main material	Zinc diecast, nickel-plated
Number of poles	5	Plugging cycles	≥ 100
Pollution severity	2	Protection degree	IP67
Sealing material	NBR	Shielding	unshielded
Type of interlock	Push Pull	Type of mounting	4 screws
UL 94 flammability rating	V-2	Wire connection cross section, finely stranded, max.	2.5 mm ²
Wire connection cross section, finely stranded, min.	0.75 mm ²		

Electrical properties

Current-carrying capacity at 50 °C	16 A	Operating voltage	24 V
------------------------------------	------	-------------------	------

General standards

Certificate No. (UR)	E92202	Connector standard	in accordance with PROFINET specification, IEC 61076-3-126
----------------------	--------	--------------------	--

Standards

Connector standard	in accordance with PROFINET specification, IEC 61076-3-126
--------------------	--

Classifications

ETIM 6.0	EC001121	ETIM 7.0	EC001121
ETIM 8.0	EC001121	ECLASS 9.0	27-44-03-90
ECLASS 9.1	27-44-03-90	ECLASS 10.0	27-44-03-90
ECLASS 11.0	27-44-03-90	ECLASS 12.0	27-44-03-90

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E92202

Erstellungs-Datum May 15, 2023 4:29:25 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

IE-BSS-VAPM-24V

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Downloads

Approval/Certificate/Document of Conformity	PROFINET Manufacturer's Declaration
Engineering Data	CAD data – STEP
Product Change Notification	Technische Änderung der Bedruckung auf PushPull Power Kontakteinsätzen Technical change to printing on PushPull Power contact inserts
User Documentation	Designation key / Type key Manual
Catalogues	Catalogues in PDF-format


IE-BSS-VAPM-24V

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


Zeichnungen

www.weidmueller.com

Dimensioned drawing



Drawing



When using wire-end-ferrules, we recommend the length of 10 mm.