

FF-EMC 22 54/230V GY**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



For use near electromagnetic fields. Secure contact surface without the need for a beryllium copper seal and particularly environmentally friendly as no metal reinforced plastics are required.

General ordering data

Version	Filter fan, IP54, grey
Order No.	2557270000
Type	FF-EMC 22 54/230V GY
GTIN (EAN)	4050118567908
Qty.	1 Stück

FF-EMC 22 54/230V GY

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	75 mm	Depth (inches)	2.953 inch
Height	145 mm	Height (inches)	5.709 inch
Width	145 mm	Width (inches)	5.709 inch
Net weight	760 g		

Temperatures

Operating temperature range	-40...55 °C
-----------------------------	-------------

General data

Colour	grey		
Current consumption	Mains frequency	50 Hz	
	Current	0.12 A	
	Mains frequency	60 Hz	
	Current	0.18 A	
EMC version	EN 61000-3-2,-3, EN 61000-6-2, 3		
Fan type	Shelf		
Filter class	G 4		
Fuse	6 A		
Height of installation cut-outs	126.5 mm		
MTBF	37,500 h		
Mounting depth	70 mm		
Mounting height	5 mm		
Noise emission	44 dB(A)		
Operating temperature range	-40...55 °C		
Power	Mains frequency	50 Hz	
	nominal	19 W	
	Mains frequency	60 Hz	
	nominal	18 W	
Protection class (UL)	Type 12		
Rated AC voltage	230 V		
Rated voltage	230 V AC \pm 10%		
Size	2		
Type of connection	Terminal strip		
Type of mounting	Snap-on		
UL 94 flammability rating	V-0		
Volume flow with exhaust filter	Mains frequency	50 Hz	
	Volume flow	44 m ³ /h	
	Exhaust filter	IP54	
	Mains frequency	60 Hz	
	Volume flow	52 m ³ /h	
	Exhaust filter	IP54	
Volume flow, free-blowing	Mains frequency	50 Hz	
	Volume flow	61 m ³ /h	
	Mains frequency	60 Hz	
	Volume flow	70 m ³ /h	
Volume flow, free-blowing at 50 Hz	61 m ³ /h		
Volume flow, free-blowing at 60 Hz	70 m ³ /h		
Width of installation cut-outs	126.5 mm		
With filter	Yes		

FF-EMC 22 54/230V GY

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Classifications

ETIM 6.0	EC000320	ETIM 7.0	EC000320
ETIM 8.0	EC000320	ECLASS 9.1	27-18-07-16
ECLASS 10.0	27-18-07-16	ECLASS 11.0	27-18-07-16
ECLASS 12.0	27-18-07-16		

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
User Documentation	Installation- and operating instructions
Catalogues	Catalogues in PDF-format

FF-EMC 22 54/230V GY

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0


Fax. +49 5231 14-2083

info@weidmueller.com


Zeichnungen

Graph

Shielding effectiveness measurements



Graph



Graph

