

THSW 0°+60°C NO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

Filter fans and cabinet heaters are ideally complemented by thermostats and hygrostats. Filter fans and heaters only work when cooling or heating is actually necessary. Because of the demand-oriented thermostats and hygrostats increase the energy efficiency and save costs.

Thermostat: our compact standard solution for heater and filter fan control. Provides protection for heating systems and helps to save energy.

General ordering data

Version	Temperature switch, grey white
Order No.	2558240000
Type	THSW 0°+60°C NO
GTIN (EAN)	4050118568899
Qty.	1 Stück

THSW 0°+60°C NO

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	36 mm	Depth (inches)	1.417 inch
Height	72 mm	Height (inches)	2.835 inch
Width	40 mm	Width (inches)	1.575 inch
Net weight	50 g		

Temperatures

Operating temperature range	-20...80 °C
-----------------------------	-------------

General data

Contact design	1 NO contacts	Operating temperature range	-20...80 °C
Switching current, NO contact		Switching current, NO contact, inductive load $\cos \varphi = 0.6$	2 A
Switching difference	<7 K	Switching tolerance	±4 K
Switching voltage	240 V AC	Temperature setting range, max.	60 °C
Temperature setting range, min.	0.01 °C	Type of connection	Screw connection
Type of mounting	Rail		

Classifications

ETIM 6.0	EC002014	ETIM 7.0	EC002014
ETIM 8.0	EC004587	ECLASS 9.1	27-21-07-07
ECLASS 10.0	27-21-07-07	ECLASS 11.0	27-21-07-07
ECLASS 12.0	27-21-07-07		

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E497840

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
Engineering Data	CAD data – STEP
User Documentation	Operating instructions
Catalogues	Catalogues in PDF-format