

**HDC MHP200 F 35****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

**General ordering data**

Version	Female, silver, 35 mm <sup>2</sup>
Order No.	<a href="#">2514830000</a>
Type	HDC MHP200 F 35
GTIN (EAN)	4050118528473
Qty.	10 Stück

## HDC MHP200 F 35

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Net weight 25 g

### Temperatures

Limit temperature -40 °C ... 125 °C

### General data

Conductor cross-section, max.	35 mm <sup>2</sup>	Cross-section for connected wire	35 mm <sup>2</sup>
Material	Copper alloy	Production methods	turned
Stripping length, rated connection	19 mm	Surface finish	silver
Type	Female	Type of connection	Crimp connection

### Classifications

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ECLASS 9.0	27-44-02-04
ECLASS 9.1	27-44-02-04	ECLASS 10.0	27-44-02-04
ECLASS 11.0	27-44-02-04	ECLASS 12.0	27-44-02-04

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

HDC MHP200 F 35

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

Zeichnungen

[www.weidmueller.com](http://www.weidmueller.com)

