


**VPU PV II 3 1000**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Product image**



**General ordering data**

Version	Surge voltage arrester, Low voltage
Order No.	<a href="#">2530550000</a>
Type	VPU PV II 3 1000
GTIN (EAN)	4050 118540550
Qty.	1 Stück
Replacement parts	<a href="#">2530660000</a>

Erstellungs-Datum May 22, 2023 4:17:37 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## VPU PV II 3 1000

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	70 mm	Depth (inches)	2.756 inch
Height	96 mm	Height (inches)	3.78 inch
Width	54 mm	Width (inches)	2.126 inch
Mounting dimension - height	75 mm	Net weight	386 g

### Temperatures

Storage temperature	85 °C	Operating temperature	-40 °C...85 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	85 °C
Humidity	5 - 95% rel. humidity		

### Rated data UL

Ambient temperature (operational), max. 85 °C	Rated Voltage $U_N$	1,100 V	
SCCR	50 kA	$I_n$	20 kA
Category	SPD TYPE 1CA	Ambient temperature (operational), min. -40 °C	
Certificate No. (cURus)	E354261	VPR ( DC+/DC-)	2,500 V
Voltage type	DC		

### General data

Colour	black, orange	Design	Installation housing; 3TE, Insta IP 20
Operating altitude	≤ 4000 m	Optical function display	green = OK; red = arrester is defective - replace
Protection degree	IP20	Rail	TS 35
UL 94 flammability rating	V-0		

### Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

### Photovoltaic technical data

Discharge current $I_n$ (8/20 μs)	20 kA	Discharge current, max. (8/20 μs)	40 kA
Operating height in the grounded PV system	≤ 2000 m	Operating height in ungrounded PV system	< 4,000 m, see operating instructions
PV system voltage, max. $U_{cpv}$	1,100 V	Protection level $U_p$ (+/-, -/PE, +/-PE)	≤ 3.8 kV
Requirements class	Type II	Short-circuit current $I_{SCPV}$	11,000 A
Standards	EN 61643-31, EN 50539-11, UL 1449	Total discharge current $I_{total}$ ( 8/20μs)	50 kA

### Rated data IEC / EN

Discharge current, max. (8/20 μs)	40 kA	Leakage current at $U_n$	30 μA
Number of poles	3	Rated voltage (DC)	1000 V
Response time	≤ 25 ns	SPD type	T2
Signalling contact	No	Standards	EN 61643-31, EN 50539-11, UL 1449
Voltage type	DC		

## VPU PV II 3 1000

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Connection data

Stripping length	18 mm	Type of connection	Screw connection
Stripping length, rated connection	18 mm	Tightening torque, min.	2 Nm
Tightening torque, max.	4 Nm	Clamping range, rated connection	16 mm <sup>2</sup>
Clamping range, min.	1.5 mm <sup>2</sup>	Clamping range, max.	35 mm <sup>2</sup>
Wire cross-section, solid, min.	1.5 mm <sup>2</sup>	Wire cross-section, solid, max.	16 mm <sup>2</sup>
Wire connection cross section, finely stranded, min.	1.5 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	25 mm <sup>2</sup>
Connection cross-section, stranded, min.	1.5 mm <sup>2</sup>	Connection cross-section, stranded, max.	35 mm <sup>2</sup>

### Guarantee

Time interval	5 years
---------------	---------

### Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ECLASS 9.0	27-13-08-05
ECLASS 9.1	27-13-08-05	ECLASS 10.0	27-13-08-05
ECLASS 11.0	27-13-08-05	ECLASS 12.0	27-17-90-90

### Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E354261

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">EAC VPU SERIES</a> <a href="#">CE VPU PV</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">EPLAN</a>
Tender specification	<a href="#">Ausschreibungstext DE</a> <a href="#">Tenderspecification EN</a>
User Documentation	<a href="#">Beipackzettel / Instruction sheet</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>


VPU PV II 3 1000

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

Zeichnungen

Electric symbol



Circuit diagram