

VPU PV I+II OM 1500

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image**General ordering data**

Version	Surge voltage arrester, Low voltage, Accessories, Spare arrester
Order No.	2534330000
Type	VPU PV I+II OM 1500
GTIN (EAN)	4050118546002
Qty.	9 Stück

Erstellungs-Datum May 22, 2023 4:19:33 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

VPU PV I+II OM 1500

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	79 mm	Depth (inches)	3.11 inch
Height	45 mm	Height (inches)	1.772 inch
Width	18 mm	Width (inches)	0.709 inch
Net weight	67 g		

Temperatures

Storage temperature	85 °C	Operating temperature	-40 °C...85 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	85 °C
Humidity	5 - 95% rel. humidity		

Rated data UL

Ambient temperature (operational), max. 85 °C	Rated Voltage U_N	750 V	
SCCR	65 kA	I_n	20 kA
Category	SPD TYPE 1CA	Ambient temperature (operational), min. -40 °C	
Certificate No. (cURus)	E354261	VPR (DC+/DC-)	4,000 V
Voltage type	DC		

General data

Colour	orange	Operating altitude	< 4,000 m, see operating instructions
Optical function display	green = OK; red = arrester is defective - replace	Protection degree	IP20
UL 94 flammability rating	V-0	Version	Spare arrester

Insulation coordination acc. to EN 50178

Pollution severity	2	Surge voltage category	III
--------------------	---	------------------------	-----

Photovoltaic technical data

Discharge current I_n (8/20 μ s)	20 kA	Discharge current, max. (8/20 μ s)	30 kA
Lightning test current I_{imp} (10/350 μ s)	5 kA	Operating height in the grounded PV system	\leq 2000 m
PV system voltage, max. U_{cpv}	1,500 V	Protection level U_p (+/- , -/PE , +/PE)	\leq 5,0 kV
Requirements class	Type I/II	Short-circuit current I_{SCPV}	11,000 A
Standards	EN 61643-31, EN 50539-11, UL 1449	Total discharge current I_{total} (8/20 μ s)	40 kA
Total discharge current I_{total} (10/350 μ s)	10 kA		

Rated data IEC / EN

Discharge current, max. (8/20 μ s)	30 kA	Leakage current at U_n	30 μ A
Lightning test current I_{imp} (10/350 μ s)	5 kA	Number of poles	1
Response time	\leq 25 ns	SPD type	T1, T2
Standards	EN 61643-31, EN 50539-11, UL 1449	Voltage type	DC

Connection data

Type of connection	pluggable
--------------------	-----------

Erstellungs-Datum May 22, 2023 4:19:33 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

VPU PV I+II 0M 1500

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Garantie

Time interval 5 years

Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ECLASS 9.0	27-13-08-05
ECLASS 9.1	27-13-08-05	ECLASS 10.0	27-13-08-05
ECLASS 11.0	27-13-08-05	ECLASS 12.0	27-17-90-90

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E354261

Downloads

Approval/Certificate/Document of Conformity	EAC VPU SERIES CE VPU PV
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

Zeichnungen

Electric symbol

