

PRO INSTA 16W 24V 0.7A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



The single-phase INSTA-POWER switching power supplies are characterised by a wide power spectrum, compact design and good value for money. They are suitable for temperature ranges from -25°C to +70°C, have international approvals and a wide voltage input range. This makes them suitable for a wide range of applications. This also includes signal and telecommunications systems as well as automation systems with a low power requirement up to 96 Watt.

General ordering data

Version	Power supply, switch-mode power supply unit, 24 V
Order No.	2580180000
Type	PRO INSTA 16W 24V 0.7A
GTIN (EAN)	4050118590913
Qty.	1 Stück

Erstellungs-Datum June 2, 2023 11:11:57 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

PRO INSTA 16W 24V 0.7A

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	60 mm	Depth (inches)	2.362 inch
Height	90.5 mm	Height (inches)	3.563 inch
Width	22.5 mm	Width (inches)	0.886 inch
Net weight	82 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-25 °C...70 °C
Operating temperature, min.	-25 °C	Operating temperature, max.	70 °C

Input

AC current consumption	0.25 A @ 230 V AC / 0.45 A @ 100 V AC	AC input voltage range	85...264 V AC (derating at 100 V AC)
Connection system	PUSH IN with actuator	DC current consumption	0.08 A @ 370V DC / 0.22 A @ 120 V DC
DC input voltage range	95...370 V DC	Frequency range AC	45...65 Hz
Input fuse (internal)	Yes	Inrush current	max. 40 A
Nominal power consumption	19.4 VA	Rated input voltage	110...240 V AC / 120...340 V DC
Recommended back-up fuse	2 A / DI, safety fuse 6 A, Char. B, circuit breaker 2...4 A, Char. C circuit breaker	Wire connection method	PUSH IN with actuator

Output

Capacitive load	unrestricted	Connection system	PUSH IN
Continuous output current @ U _{Nominal}	0.7 A @ 55 °C, 0.43 A @ 70 °C	Nominal output current for U _{nom}	0.7 A @ 55 °C
Output current, max.	0.7 A	Output power	16 W
Output voltage, max.	28 V	Output voltage, min.	22 V
Output voltage, note	(adjustable via potentiometer on front)	Ramp-up time	≤ 100 ms
Rated output voltage	24 V DC ± 1 %	Residual ripple, breaking spikes	< 50 mV _{ss} @ U _{Nenn} , Full Load
Wire connection method	PUSH IN with actuator		

General data

Degree of efficiency	82.5 %	Housing version	Plastic, protective insulation
Mounting position, installation notice	Horizontal on DIN rail TS 35, top and bottom 50 mm clearance for free air flow, 10 mm clearance to neighbouring active subassemblies with full load, 5 mm with passive neighbouring subassemblies, direct row mounting with 90% rated load	Power loss, idling	0.4 W
Power loss, nominal load	3.6 W	Protection against reverse voltages from the load	30...35 V DC
Protection degree	IP20	Short-circuit protection	internal, Yes
Start-up	≥ -40 °C		

Erstellungs-Datum June 2, 2023 11:11:57 AM CEST

PRO INSTA 16W 24V 0.7A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

EMC / shock / vibration

Interference immunity test acc. to	EN 61000-4-2 (ESD) EN 61000-4-3 and EN 61000-4-8 (fields) EN 61000-4-4 (burst) EN 61000-4-5 (surge) EN 61000-4-6 (conducted) EN 61000-4-11 (dips), EN 61000-4-11 (Dips)	Limiting of mains voltage harmonic currents	According to EN 61000-3-2
Noise emission in accordance with EN55032	Class B	Shock resistance IEC 60068-2-27	15 g In all directions
Vibration resistance IEC 60068-2-6	2.3 g		

Insulation coordination

Insulation voltage input / earth	3.5 kV	Insulation voltage output / earth	0.5 kV
Insulation voltage, input/output	4 kV	Pollution severity	2
Protection class	II		

Electrical safety (applied standards)

Electrical machine equipment	Acc. to EN60204	For use with electronic equipment	Acc. to EN50178 / VDE0160
Protection against dangerous shock currents	Acc. to VDE0106-101	Protective separation / protection against electrical shock	VDE0100-410 / acc. to DIN57100-410
Safety extra-low voltage	SELV acc. to IEC 60950-1, PELV according to EN 60204-1	Safety transformers for switch-mode power supplies	According to EN 61558-2-16

Connection data (input)

Conductor cross-section, AWG/kcmil , max.	12	Conductor cross-section, AWG/kcmil , min.	24
Conductor cross-section, flexible , min.	0.25 mm ²	Conductor cross-section, rigid , max.	2.5 mm ²
Conductor cross-section, rigid , min.	0.25 mm ²	Connection system	PUSH IN with actuator
Wire connection cross section, flexible (input), max.	2.5 mm ²		

Connection data (output)

Conductor cross-section, AWG/kcmil , max.	12	Conductor cross-section, AWG/kcmil , min.	24
Conductor cross-section, flexible , max.	2.5 mm ²	Conductor cross-section, flexible , min.	0.25 mm ²
Conductor cross-section, rigid , max.	2.5 mm ²	Conductor cross-section, rigid , min.	0.25 mm ²
Connection system	PUSH IN	Number of terminals	2 (+ / -)

Signalling

LED green	Operating voltage OK
-----------	----------------------

Approbations

Certificate no. (cULus)	E258476	Institute (cULus)	CULUS
-------------------------	---------	-------------------	-------

PRO INSTA 16W 24V 0.7A

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Classifications

ETIM 6.0	EC002540	ETIM 7.0	EC002540
ETIM 8.0	EC002540	ECLASS 9.0	27-04-07-01
ECLASS 9.1	27-04-07-01	ECLASS 10.0	27-04-07-01
ECLASS 11.0	27-04-07-01	ECLASS 12.0	27-04-07-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Lead monoxide 1317-36-8
SCIP	d62541f7-8058-4336-b693-7303c8b40800

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E258476

Downloads

Approval/Certificate/Document of Conformity	Declaration of Conformity
Engineering Data	CAD data – STEP
Engineering Data	EPLAN
User Documentation	Operating instruction
Catalogues	Catalogues in PDF-format

PRO INSTA 16W 24V 0.7A

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

