

THM ET DIA 55 WS

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system M-Print® PRO under Windows optimise all labelling efforts.

- High-quality polyester labels in different colours
- Due to their flexible material and the thick adhesive layer, the THM GEW can be used on angled or round objects such as cables or hoses
- Roll-packaged THM ET S7 can be used to label the Simatic 200S, S7-300 and S7-400 modules from Siemens
- Labels are automatically positioned in the printer for perfectly centred prints on each label.
- Labelling with the THM MultiMark or THM MultiMark Plus thermal transfer printers

General ordering data

| | |
|------------|------------------------------------|
| Version | Conductor and cable markers, white |
| Order No. | 2539400000 |
| Type | THM ET DIA 55 WS |
| GTIN (EAN) | 4050118570168 |
| Qty. | 1,000 Stück |

THM ET DIA 55 WS

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|----------|---------|----------------|------------|
| Depth | 0.35 mm | Depth (inches) | 0.014 inch |
| Diameter | 55 mm | Net weight | 1.216 g |

Temperatures

| | | | |
|----------------------------------|--------------|----------------------------------|-----|
| Operating temperature range | -50...100 °C | Continuous operating temp., min. | -50 |
| Continuous operating temp., max. | 100 | | |

General data

| | | | |
|-----------------------------------|---------------|-----------------------------------|--------------|
| Colour | white | Halogen | No |
| Material | Polypropylene | Operating temperature range | -50...100 °C |
| Operating temperature range, max. | 100 °C | Operating temperature range, min. | -50 °C |
| UL 94 flammability rating | HB | | |

Conductor and cable markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ECLASS 9.0 | 27-40-06-29 |
| ECLASS 9.1 | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|------------------------------------------|
| Engineering Data | EPLAN |
| Catalogues | Catalogues in PDF-format |

THM ET DIA 55 WS

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Zeichnungen

