

**CBC-SP 8-70/25 TP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Spiral and webbing hoses are particularly suitable for the construction of space-saving cable routing systems in switch gears and control cabinets. They are used for guiding, protecting and bundling cables and wires - for example, in the transition between the enclosure interior and the door.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Version    | Protective cable hose coil |
| Order No.  | <a href="#">2588780000</a> |
| Type       | CBC-SP 8-70/25 TP          |
| GTIN (EAN) | 4050118602401              |
| Qty.       | 25 m                       |

Erstellungs-Datum June 1, 2023 10:11:04 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

## CBC-SP 8-70/25 TP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Dimensions and weights

|          |            |                 |            |
|----------|------------|-----------------|------------|
| Length   | 100,000 mm | Length (inches) | 3,937 inch |
| Diameter | 8 mm       | Net weight      | 20 g       |

### Temperatures

|                             |             |                             |        |
|-----------------------------|-------------|-----------------------------|--------|
| Operating temperature range | -15...60 °C | Operating temperature, min. | -15 °C |
| Operating temperature, max. | 60 °C       |                             |        |

### General information

|                             |              |                       |                       |
|-----------------------------|--------------|-----------------------|-----------------------|
| Bundle diameter, max.       | 70 mm        | Bundle diameter, min. | 8 mm                  |
| Colour                      | Transparent  | Diameter              | 8 mm                  |
| Material                    | Polyethylene | Nominal diameter      | 6 mm                  |
| Operating temperature range | -15...60 °C  | Usable cross-section  | 3,848 mm <sup>2</sup> |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001182    | ETIM 7.0    | EC001182    |
| ETIM 8.0    | EC001182    | ECLASS 9.1  | 27-43-03-03 |
| ECLASS 10.0 | 27-43-03-03 | ECLASS 11.0 | 27-43-03-03 |
| ECLASS 12.0 | 27-43-03-03 |             |             |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|--|