


VPU AC II 0 350/50

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



In the event of a defective arrester, you can easily reorder this spare arrester, replace the defective arrester and thus restore protection.

General ordering data

Version	Spare arrester, Surge protection, $U_p(L/N-PE) \leq 1.75 \text{ kV}$
Order No.	2591340000
Type	VPU AC II 0 350/50
GTIN (EAN)	4050118599596
Qty.	1 Stück

VPU AC II 0 350/50

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	64 mm	Depth (inches)	2.52 inch
Height	45 mm	Height (inches)	1.772 inch
Width	18 mm	Width (inches)	0.709 inch
Net weight	65 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	85 °C
Humidity	5 - 95% rel. humidity		

Rated data UL

Ambient temperature (operational), max.	85 °C	Rated Voltage U_N	277 V
VPR (N-PE)	1,000 V	MCOV (L/N-PE)	350 V
SCCR	200 kA	I_n	20 kA
Category	SPD TYPE 1CA	Ambient temperature (operational), min.	-40 °C
Certificate No. (cURus)	E354261	VPR (L-PE)	1,000 V
Voltage type	AC		

General data

Colour	orange	Operating altitude	≤ 2000 m
Optical function display	green = OK; red = arrester is defective - replace	Protection degree	IP20 in installed state
Rail	TS 35	Segment	Power distribution
UL 94 flammability rating	V-0	Version	Surge protection

Rated data IEC / EN

Discharge current I_{max} (8/20 μ s) wire-PE	50 kA	Energy coordination (≤10 m)	Type II, Type III
Follow-on current extinguishing capability I_{fi}	Follow current need not be taken into account	Frequency range, max.	60 Hz
Frequency range, min.	50 Hz	Leakage current at U_n	0.3 mA
Max. continuous voltage, U_c (AC)	350 V	Number of poles	1
Protection level U_p (typ.)	≤ 1.75 kV	Rated voltage (AC)	230 V
Requirements category acc. to IEC 61643-11	Type II	Requirements class, acc. to EN 61643-11	T2
Response time	≤ 25 ns	Standards	IEC61643-11, EN61643-11, UL 1449
Voltage type	AC		

Connection data

Type of connection	Plug-in connection
--------------------	--------------------

Guarantee

Time interval	5 years
---------------	---------

VPU AC II 0 350/50

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Classifications

ETIM 6.0	EC000941	ETIM 7.0	EC000941
ETIM 8.0	EC000941	ECLASS 9.0	27-13-08-05
ECLASS 9.1	27-13-08-05	ECLASS 10.0	27-13-08-05
ECLASS 11.0	27-13-08-05	ECLASS 12.0	27-17-90-90

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E354261

Downloads

Approval/Certificate/Document of Conformity	EAC VPU SERIES EU Konformitätserklärung / EU Declaration of Conformity
User Documentation	Beipackzettel / Instruction sheet
Catalogues	Catalogues in PDF-format

Zeichnungen

Electric symbol

