

## PRO INSTA 30W 5V 6A

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



The single-phase INSTA-POWER switching power supplies are characterised by a wide power spectrum, compact design and good value for money. They are suitable for temperature ranges from -25°C to +70°C, have international approvals and a wide voltage input range. This makes them suitable for a wide range of applications. This also includes signal and telecommunications systems as well as automation systems with a low power requirement up to 96 Watt.

### General ordering data

Version	Power supply, switch-mode power supply unit, 5 V
Order No.	<a href="#">2580210000</a>
Type	PRO INSTA 30W 5V 6A
GTIN (EAN)	4050118590937
Qty.	1 Stück

Erstellungs-Datum June 2, 2023 11:12:15 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

## PRO INSTA 30W 5V 6A

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	60 mm	Depth (inches)	2.362 inch
Height	90 mm	Height (inches)	3.543 inch
Width	72 mm	Width (inches)	2.835 inch
Net weight	256 g		

### Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-25 °C...70 °C
Operating temperature, min.	-25 °C	Operating temperature, max.	70 °C

### Input

AC current consumption	0.5 A @ 230 V AC / 1.0 A @ 100 V AC	AC input voltage range	85...264 V AC (derating at 100 V AC)
Connection system	PUSH IN with actuator	DC current consumption	0.2 A @ 370 V DC / 0.5 A @ 120 V DC
DC input voltage range	95...370 V DC	Frequency range AC	45...65 Hz
Input fuse (internal)	Yes	Inrush current	max. 40 A
Nominal power consumption	36.6 VA	Rated input voltage	110...240 V AC / 120...340 V DC
Recommended back-up fuse	2 A / DI, safety fuse 6 A, Char. B, circuit breaker 2...4 A, Char. C circuit breaker	Wire connection method	PUSH IN with actuator

### Output

Capacitive load	unrestricted	Connection system	PUSH IN
Continuous output current @ U <sub>Nominal</sub>	6 A @ 55 °C, 3.75 A @ 70 °C	Nominal output current for U <sub>nom</sub>	6 A @ 55 °C
Output current, max.	6 A	Output power	30 W
Output voltage, max.	7 V	Output voltage, min.	4 V
Output voltage, note	(adjustable via potentiometer on front)	Ramp-up time	≤ 100 ms
Rated output voltage	5 V DC ± 2 %	Residual ripple, breaking spikes	< 50 mV <sub>ss</sub> @ U <sub>Nenn</sub> , Full Load
Wire connection method	PUSH IN with actuator		

### General data

Degree of efficiency	82 %	Housing version	Plastic, protective insulation
Mounting position, installation notice	Horizontal on DIN rail TS 35, top and bottom 50 mm clearance for free air flow, 10 mm clearance to neighbouring active subassemblies with full load, 5 mm with passive neighbouring subassemblies, direct row mounting with 90% rated load	Power loss, idling	0.45 W
Power loss, nominal load	5.4 W	Protection against reverse voltages from the load	8...10 V DC
Protection degree	IP20	Short-circuit protection	Yes, internal
Start-up	≥ -40 °C		

Erstellungs-Datum June 2, 2023 11:12:15 AM CEST

## PRO INSTA 30W 5V 6A

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### EMC / shock / vibration

Interference immunity test acc. to	EN 61000-4-2 (ESD)  EN 61000-4-3 and EN 61000-4-8 (fields) EN 61000-4-4 (burst) EN 61000-4-5 (surge) EN 61000-4-6 (conducted)  EN 61000-4-11 (dips), EN 61000-4-11 (Dips)	Limiting of mains voltage harmonic currents	EN 61000-4-2 (ESD)  EN 61000-4-3 and EN 61000-4-8 (fields) EN 61000-4-4 (burst) EN 61000-4-5 (surge) EN 61000-4-6 (conducted)  EN 61000-4-11 (dips), EN 61000-4-11 (Dips)
Noise emission in accordance with EN55032	Class B	Shock resistance IEC 60068-2-27	15 g In all directions
Vibration resistance IEC 60068-2-6	2.3 g		

### Insulation coordination

Insulation voltage input / earth	3.5 kV	Insulation voltage output / earth	0.5 kV
Insulation voltage, input/output	4 kV	Pollution severity	2
Protection class	II		

### Electrical safety (applied standards)

Electrical machine equipment	Acc. to EN60204	For use with electronic equipment	Acc. to EN50178 / VDE0160
Protection against dangerous shock currents	Acc. to VDE0106-101	Protective separation / protection against electrical shock	VDE0100-410 / acc. to DIN57100-410
Safety extra-low voltage	SELV acc. to IEC 60950-1, PELV according to EN 60204-1	Safety transformers for switch-mode power supplies	According to EN 61558-2-16

### Connection data (input)

Conductor cross-section, AWG/kcmil , max.	12	Conductor cross-section, AWG/kcmil , min.	24
Conductor cross-section, flexible , min.	0.25 mm <sup>2</sup>	Conductor cross-section, rigid , max.	2.5 mm <sup>2</sup>
Conductor cross-section, rigid , min.	0.25 mm <sup>2</sup>	Connection system	PUSH IN with actuator
Wire connection cross section, flexible (input), max.	2.5 mm <sup>2</sup>		

### Connection data (output)

Conductor cross-section, AWG/kcmil , max.	12	Conductor cross-section, AWG/kcmil , min.	24
Conductor cross-section, flexible , max.	2.5 mm <sup>2</sup>	Conductor cross-section, flexible , min.	0.25 mm <sup>2</sup>
Conductor cross-section, rigid , max.	2.5 mm <sup>2</sup>	Conductor cross-section, rigid , min.	0.25 mm <sup>2</sup>
Connection system	PUSH IN	Number of terminals	4 ( ++ / - )

### Signalling

LED green	Operating voltage OK
-----------	----------------------

### Approbations

Certificate no. (cULus)	E258476	Institute (cULus)	CULUS
-------------------------	---------	-------------------	-------

## PRO INSTA 30W 5V 6A

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Classifications

ETIM 6.0	EC002540	ETIM 7.0	EC002540
ETIM 8.0	EC002540	ECLASS 9.0	27-04-07-01
ECLASS 9.1	27-04-07-01	ECLASS 10.0	27-04-07-01
ECLASS 11.0	27-04-07-01	ECLASS 12.0	27-04-07-01

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Lead monoxide 1317-36-8
SCIP	d62541f7-8058-4336-b693-7303c8b40800

### Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E258476

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">EPLAN</a>
User Documentation	<a href="#">Operating instruction</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**PRO INSTA 30W 5V 6A**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

