

**CB-HTR 140/3,5 NC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Our heat-stabilised cable ties made of polyamide 6.6 are suitable for continuous use at temperatures up to +125°C.

**General ordering data**

|            |   |
|------------|---|
| Version    | Cable ties, 3.5 x 140 mm, Polyamide 66, 180 N |
| Order No.  | <a href="#">2659440000</a>                    |
| Type       | CB-HTR 140/3,5 NC                             |
| GTIN (EAN) | 4050118682908                                 |
| Qty.       | 100 Stück                                     |

Erstellungs-Datum May 26, 2023 2:53:25 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## CB-HTR 140/3,5 NC

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Height     | 140 mm | Height (inches) | 5.512 inch |
| Width      | 3.5 mm | Width (inches)  | 0.138 inch |
| Net weight | 0.6 g  |                 |            |

### Temperatures

|                                  |              |                                  |        |
|----------------------------------|--------------|----------------------------------|--------|
| Operating temperature range      | -40...125 °C | Operating temperature, min.      | -40 °C |
| Operating temperature, max.      | 125 °C       | Continuous operating temp., min. | -40 °C |
| Continuous operating temp., max. | 125 °C       |                                  |        |

### Installation materials

|                                   |        |                                   |              |
|-----------------------------------|--------|-----------------------------------|--------------|
| Bundle diameter, max.             | 32 mm  | Bundle diameter, min.             | 2.5 mm       |
| Cable diameter, max.              | 35 mm  | For re-opening                    | No           |
| Halogen                           | No     | Material                          | Polyamide 66 |
| Operating temperature range, max. | 125 °C | Operating temperature range, min. | -40 °C       |
| Tensile strength                  | 180 N  | Tensile strength (Pound-force)    | 40 lbf       |
| UL 94 flammability rating         | V-2    | UV-resistant                      | No           |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000046    | ETIM 7.0    | EC000046    |
| ETIM 8.0    | EC000046    | ECLASS 9.0  | 27-14-07-02 |
| ECLASS 9.1  | 27-14-07-02 | ECLASS 10.0 | 27-14-07-02 |
| ECLASS 11.0 | 27-14-07-02 | ECLASS 12.0 | 27-14-07-02 |

### Approvals

Approvals



ROHS

Conform

### Downloads

Approval/Certificate/Document of Conformity

[EU Declaration of Conformity](#)

Catalogues

[Catalogues in PDF-format](#)

**Datenblatt**

**CB-HTR 140/3,5 NC**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

