

PB-CON SF DELTA PT 40X12

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Product image



- Future-proof design
- Different module sizes
- Simple device integration
- Simple plug-and-play solution – fast replacement of individual modules from a single device network
- Quick and easy installation without tools
- Safe locking of busbar connectors
- Touch-safe construction
- Tolerance compensation in the rail system allows simple mounting of the devices on the panel mounting plate without extreme accuracy
- Uncomplicated UL approval with registered UL components
- Ideal design of size and technical data for typical multi-axis servo amplifiers

General ordering data

Version	PCB plug-in connector, Mounting screw
Order No.	2708620000
Type	PB-CON SF DELTA PT 40X12
GTIN (EAN)	4050118771015
Qty.	40 Stück
Product data	

PB-CON SF DELTA PT 40X12

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 1.425 g

Temperatures

Operating temperature, min. -50 °C Operating temperature, max. 100 °C

Material data

Insulating material	Steel	Storage temperature, min.	-40 °C
Storage temperature, max.	70 °C	Operating temperature, min.	-50 °C
Operating temperature, max.	100 °C	Temperature range, installation, min.	-25 °C
Temperature range, installation, max.	100 °C		

Rated data acc. to IEC

tested acc. to standard IEC 60664-1, IEC 61984

Packing

VPE length	70 mm	VPE width	42 mm
VPE height	12 mm		

Classifications

ETIM 6.0	EC000887	ETIM 7.0	EC000887
ETIM 8.0	EC003861	ECLASS 9.0	23-11-01-90
ECLASS 9.1	23-11-01-90	ECLASS 10.0	23-11-01-90
ECLASS 11.0	23-11-01-90	ECLASS 12.0	23-11-01-90

Important note

IPC conformity Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

Notes • Long term storage of the product with average temperature of 50 °C and average humidity 70%, 36 months

Approvals

ROHS Conform

Downloads

Catalogues [Catalogues in PDF-format](#)