

EPAK-VI-VO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The analogue converters of the EPAK series are characterised by their compact design. The wide range of functions available with this series of analogue converters make them suitable for applications which do not require international approvals.

Properties:

- Safe isolation, conversion and monitoring of your analogue signals
- Configuration of the input and output parameters directly on the device via DIP switches
- No international approvals
- High interference resistance

General ordering data

Order No.	7760054175
Type	EPAK-VI-VO
GTIN (EAN)	6944 169701467
Qty.	1 Stück

EPAK-VI-VO

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	89 mm	Depth (inches)	3.504 inch
Width	17.5 mm	Width (inches)	0.689 inch
Length	100 mm	Length (inches)	3.937 inch
Net weight	80 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-20 °C...60 °C
Operating temperature, min.	-20 °C	Operating temperature, max.	60 °C
Humidity	5 to 95 % (non-condensing)		

Input

Input resistance, voltage	≥ 100 kΩ	Input voltage	0...10 V
---------------------------	----------	---------------	----------

Output

Output voltage, note	0...10 V	load impedance voltage	≥ 10 kΩ
----------------------	----------	------------------------	---------

General data

Accuracy	0.15 % v. FSR	Configuration	none
Galvanic isolation	between input/output/supply	Power consumption	<60mA @ 24VDC
Step response time	≤ 100 ms	Temperature coefficient	≤ 150 ppm/K
Voltage supply	20...30 V DC		

Insulation coordination

EMC standards	EN 61326	Galvanic isolation	between input/output/supply
Impulse withstand voltage	3 kV (1.2/50µs)	Insulation voltage	2 kV _{eff}
Pollution severity	2	Rated voltage	300 V AC _{rms}
Surge voltage category	III		

Connection data

Type of connection	Screw connection	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.6 Nm	Clamping range, rated connection	2 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	2 mm ²
Wire connection cross section AWG, min.	AWG 30	Wire connection cross section AWG, max.	AWG 14

Classifications

ETIM 6.0	EC002653	ETIM 7.0	EC002653
ETIM 8.0	EC002653	ECLASS 9.0	27-21-01-20
ECLASS 9.1	27-21-01-90	ECLASS 10.0	27-21-01-20
ECLASS 11.0	27-21-01-20	ECLASS 12.0	27-21-01-20

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6a722fc5-2d22-41b4-9544-5b95e45a4b77

Erstellungs-Datum June 1, 2023 10:49:23 AM CEST

EPAK-VI-VO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of
Conformity

[Declaration of Conformity](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[Instruction sheet](#)

Catalogues

[Catalogues in PDF-format](#)

EPAK-VI-VO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

