

## EPAK-PCI-VO

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



The analogue converters of the EPAK series are characterised by their compact design. The wide range of functions available with this series of analogue converters make them suitable for applications which do not require international approvals.

Properties:

- Safe isolation, conversion and monitoring of your analogue signals
- Configuration of the input and output parameters directly on the device via DIP switches
- No international approvals
- High interference resistance

### General ordering data

|            |                            |
|------------|----------------------------|
| Order No.  | <a href="#">7760054177</a> |
| Type       | EPAK-PCI-VO                |
| GTIN (EAN) | 6944 169701481             |
| Qty.       | 1 Stück                    |

## EPAK-PCI-VO

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 89 mm   | Depth (inches)  | 3.504 inch |
| Width      | 17.5 mm | Width (inches)  | 0.689 inch |
| Length     | 100 mm  | Length (inches) | 3.937 inch |
| Net weight | 80 g    |                 |            |

### Temperatures

|                             |                |                             |                |
|-----------------------------|----------------|-----------------------------|----------------|
| Storage temperature         | -40 °C...85 °C | Operating temperature       | -20 °C...60 °C |
| Operating temperature, min. | -20 °C         | Operating temperature, max. | 60 °C          |

### Input

|               |   |                           |                |
|---------------|---|---------------------------|----------------|
| Input current | 4...20 mA                                     | Input resistance, current | ≤ 100 Ω        |
| Sensor        | 2-wire transmitter (without own power supply) | Sensor supply             | ≥ 18 V @ 20 mA |

### Output

|                      |          |                        |         |
|----------------------|----------|------------------------|---------|
| Output voltage, note | 0...10 V | load impedance voltage | ≥ 10 kΩ |
|----------------------|----------|------------------------|---------|

### General data

|                    |                             |                         |               |
|--------------------|-----------------------------|-------------------------|---------------|
| Accuracy           | 0.15 % v. FSR               | Configuration           | none          |
| Galvanic isolation | between input/output/supply | Power consumption       | <60mA @ 24VDC |
| Step response time | ≤ 100 ms                    | Temperature coefficient | ≤ 150 ppm/K   |
| Voltage supply     | 20...30 V DC                |                         |               |

### Insulation coordination

|                           |                 |                    |                             |
|---------------------------|-----------------|--------------------|-----------------------------|
| EMC standards             | EN 61326        | Galvanic isolation | between input/output/supply |
| Impulse withstand voltage | 3 kV (1.2/50μs) | Insulation voltage | 2 kV <sub>eff</sub>         |
| Pollution severity        | 2               | Rated voltage      | 300 V AC <sub>rms</sub>     |
| Surge voltage category    | III             |                    |                             |

### Connection data

|   |                     |   |                   |
|---|---------------------|---|-------------------|
| Type of connection                      | Screw connection    | Tightening torque, min.                 | 0.4 Nm            |
| Tightening torque, max.                 | 0.6 Nm              | Clamping range, rated connection        | 2 mm <sup>2</sup> |
| Clamping range, min.                    | 0.5 mm <sup>2</sup> | Clamping range, max.                    | 2 mm <sup>2</sup> |
| Wire connection cross section AWG, min. | AWG 30              | Wire connection cross section AWG, max. | AWG 14            |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002653    | ETIM 7.0    | EC002653    |
| ETIM 8.0    | EC002653    | ECLASS 9.0  | 27-21-01-20 |
| ECLASS 9.1  | 27-21-01-90 | ECLASS 10.0 | 27-21-01-20 |
| ECLASS 11.0 | 27-21-01-20 | ECLASS 12.0 | 27-21-01-20 |

### Environmental Product Compliance

|            |                                      |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1                       |
| SCIP       | 6a722fc5-2d22-41b4-9544-5b95e45a4b77 |

Erstellungs-Datum June 1, 2023 10:49:48 AM CEST

## EPAK-PCI-VO

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Approvals

Approvals



ROHS

Conform

### Downloads

Approval/Certificate/Document of  
Conformity

[Declaration of Conformity](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[Instruction sheet](#)

Catalogues

[Catalogues in PDF-format](#)

**EPAK-PCI-VO**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

