

## EPAK-2CI-2CO-ILP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The analogue converters of the EPAK series are characterised by their compact design. The wide range of functions available with this series of analogue converters make them suitable for applications which do not require international approvals.

Properties:

- Safe isolation, conversion and monitoring of your analogue signals
- Configuration of the input and output parameters directly on the device via DIP switches
- No international approvals
- High interference resistance

### General ordering data

Order No.	<a href="#">7760054180</a>
Type	EPAK-2CI-2CO-ILP
GTIN (EAN)	6944 169701511
Qty.	1 Stück

## EPAK-2CI-2CO-ILP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	89 mm	Depth (inches)	3.504 inch
Width	17.5 mm	Width (inches)	0.689 inch
Length	100 mm	Length (inches)	3.937 inch
Net weight	80 g		

### Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-20 °C...60 °C
Operating temperature, min.	-20 °C	Operating temperature, max.	60 °C
Humidity at operating temperature	5...95 %, no condensation		

### Input

Input current	4...20 mA (current loop)	Input signal	Current source
Number of inputs	2	Voltage drop, current input	≤30 V

### Output

Load impedance current	≤450 Ω	Number of outputs	2
Output current	4...20 mA		

### Output (analogue)

Output current	4...20 mA
----------------	-----------

### General data

Accuracy	0.15 % v. FSR	Configuration	none
Galvanic isolation	between input/output	Step response time	≤ 100 ms
Temperature coefficient	≤ 150 ppm/K	Voltage supply	Loop powered, via 4...20 mA input

### Insulation coordination

EMC standards	EN 61326	Galvanic isolation	between input/output
Impulse withstand voltage	4 kV (1.2/50 μs)	Insulation voltage	2 kV <sub>eff</sub>
Pollution severity	2	Rated voltage	300 V AC <sub>rms</sub>
Surge voltage category	III		

### Connection data

Type of connection	Screw connection	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.6 Nm	Clamping range, rated connection	2 mm <sup>2</sup>
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping range, max.	2 mm <sup>2</sup>
Wire connection cross section AWG, min.	AWG 30	Wire connection cross section AWG, max.	AWG 14

### Classifications

ETIM 6.0	EC002653	ETIM 7.0	EC002653
ETIM 8.0	EC002653	ECLASS 9.0	27-21-01-20
ECLASS 9.1	27-21-01-20	ECLASS 10.0	27-21-01-20
ECLASS 11.0	27-21-01-20	ECLASS 12.0	27-21-01-20

## EPAK-2CI-2CO-ILP

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6a722fc5-2d22-41b4-9544-5b95e45a4b77

### Approvals

Approvals



ROHS	Conform
------	---------

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Instruction sheet</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**EPAK-2CI-2CO-ILP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

