

## EPAK-CMR-1PH-5-230V

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



The analogue converters of the EPAK series are characterised by their compact design. The wide range of functions available with this series of analogue converters make them suitable for applications which do not require international approvals.

Properties:

- Safe isolation, conversion and monitoring of your analogue signals
- Configuration of the input and output parameters directly on the device via DIP switches
- No international approvals
- High interference resistance

### General ordering data

Order No.	<a href="#">7760054247</a>
Type	EPAK-CMR-1PH-5-230V
GTIN (EAN)	6944 169733796
Qty.	1 Stück

Erstellungs-Datum June 1, 2023 10:51:54 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

## EPAK-CMR-1PH-5-230V

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	89 mm	Depth (inches)	3.504 inch
Width	17.5 mm	Width (inches)	0.689 inch
Length	100 mm	Length (inches)	3.937 inch
Net weight	80 g		

### Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-20 °C...60 °C
Operating temperature, min.	-20 °C	Operating temperature, max.	60 °C

### Input

Input current	0.1...1A AC/DC, 0.5...5A AC/DC	Input frequency	40...60 Hz
Input signal	AC (sine), DC		

### Output (digital)

Alarm function	Surge current, Under-current, Alarm range: 10% ...100% *I <sub>N</sub> , Hysteresis: 5% *I <sub>N</sub> (fixed), Alarm delay: 0...10 s	Continuous current	3 A
Max. switching voltage, AC	250 V	Max. switching voltage, DC	30 V
Type	Relay, 1 CO contact		

### General data

Accuracy	5 % *I <sub>N</sub>	Configuration	DIP switch and potentiometer
Galvanic isolation	between input/output/supply/relay	Power consumption	<9 mA @230 VAC
Repeat accuracy	2 % *I <sub>N</sub>	Step response time	< 220 ms (10...90 %)
Temperature coefficient	≤ 250 ppm/K	Voltage supply	85...264 VAC

### Insulation coordination

EMC standards	IEC 61000-6 /-2, IEC 61000-6-4	Galvanic isolation	between input/output/supply/relay
Impulse withstand voltage	4 kV (1.2/50 μs)	Insulation voltage	2.2 kVAC, 1 min, 50 Hz
Pollution severity	2	Rated voltage	300 V AC <sub>rms</sub>
Surge voltage category	II		

### Connection data

Type of connection	Screw connection	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.6 Nm	Clamping range, rated connection	2 mm <sup>2</sup>
Clamping range, min.	0.5 mm <sup>2</sup>	Clamping range, max.	2 mm <sup>2</sup>
Wire connection cross section AWG, min.	AWG 30	Wire connection cross section AWG, max.	AWG 14

## EPAK-CMR-1PH-5-230V

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Classifications

ETIM 6.0	EC002654	ETIM 7.0	EC002654
ETIM 8.0	EC002654	ECLASS 9.0	27-21-01-22
ECLASS 9.1	27-21-01-22	ECLASS 10.0	27-21-01-22
ECLASS 11.0	27-21-01-22	ECLASS 12.0	27-21-01-22

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6a722fc5-2d22-41b4-9544-5b95e45a4b77

### Approvals

Approvals



ROHS	Conform
------	---------

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Instruction sheet</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## EPAK-CMR-1PH-5-230V

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Zeichnungen

