

EPAK-VMR-3PH-480-ILP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



The analogue converters of the EPAK series are characterised by their compact design. The wide range of functions available with this series of analogue converters make them suitable for applications which do not require international approvals.

Properties:

- Safe isolation, conversion and monitoring of your analogue signals
- Configuration of the input and output parameters directly on the device via DIP switches
- No international approvals
- High interference resistance

General ordering data

Order No.	7760054301
Type	EPAK-VMR-3PH-480-ILP
GTIN (EAN)	6944 169747700
Qty.	1 Stück

EPAK-VMR-3PH-480-ILP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Width	17.5 mm	Width (inches)	0.689 inch
Length	100 mm	Length (inches)	3.937 inch
Net weight	80 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-20 °C...60 °C
Operating temperature, min.	-20 °C	Operating temperature, max.	60 °C
Humidity at operating temperature	0...85 % rel. humidity		

Input

Input frequency	40...60 Hz	Input measurement range	165...550 V AC
Number of inputs	1 x three-phase (R, S, T, N)		

Output (digital)

Alarm function	Phase error, Phase sequence, Asymmetry, Window alarm: -15% for min. value (fixed), 10% for max. value (fixed), Hysteresis: 10 V	Max. switching voltage, AC	250 V
Max. switching voltage, DC	30 V	Rated switching current	3 A
Type	Relay, 1 CO contact		

General data

Accuracy	5 % of FSR	Configuration	none
Galvanic isolation	between input/output	Step response time	≤ 200 ms (10...90%)
Temperature coefficient	≤ 250 ppm/K of measuring range	Voltage supply	from the measuring circuit

Insulation coordination

EMC standards	IEC 61000-6-2, IEC 61000-6-4	Galvanic isolation	between input/output
Impulse withstand voltage	4 kV (1.2/50 µs)	Insulation voltage	2.2 kVAC, 1 min, 50 Hz
Pollution severity	2	Rated voltage	300 V
Surge voltage category	II		

Connection data

Type of connection	Screw connection	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.6 Nm	Clamping range, rated connection	2 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	2 mm ²
Wire connection cross section AWG, min.	AWG 30	Wire connection cross section AWG, max.	AWG 14

Classifications

ETIM 6.0	EC002654	ETIM 7.0	EC002654
ETIM 8.0	EC002654	ECLASS 9.0	27-21-01-22
ECLASS 9.1	27-21-01-22	ECLASS 10.0	27-21-01-22
ECLASS 11.0	27-21-01-22	ECLASS 12.0	27-21-01-22

Erstellungs-Datum June 1, 2023 10:52:30 AM CEST

EPAK-VMR-3PH-480-ILP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6a722fc5-2d22-41b4-9544-5b95e45a4b77

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Declaration of Conformity
Engineering Data	CAD data – STEP
User Documentation	Instruction sheet
Catalogues	Catalogues in PDF-format

EPAK-VMR-3PH-480-ILP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Zeichnungen

