

## CABTITE BP 9MM PA

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



The blanking plugs are used for the safe closing of unneeded cable passages in the sealing elements.

### General ordering data

|            |   |
|------------|---|
| Version    | Blind plug, Cabtite (cable entry system), Polyamide, white, Height: 16 mm, Width: 9 mm, Depth: 16 mm, -40 °C...120 °C, IP66 |
| Order No.  | <a href="#">2652370000</a>  |
| Type       | CABTITE BP 9MM PA   |
| GTIN (EAN) | 4050118662474   |
| Qty.       | 25 Stück  |

Erstellungs-Datum May 26, 2023 2:26:33 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## CABTITE BP 9MM PA

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|          |       |                 |            |
|----------|-------|-----------------|------------|
| Depth    | 16 mm | Depth (inches)  | 0.63 inch  |
| Height   | 16 mm | Height (inches) | 0.63 inch  |
| Width    | 9 mm  | Width (inches)  | 0.354 inch |
| Length   | 16 mm | Length (inches) | 0.63 inch  |
| Diameter | 9 mm  | Net weight      | 0.86 g     |

### Temperatures

|                             |                 |                             |        |
|-----------------------------|-----------------|-----------------------------|--------|
| Operating temperature       | -40 °C...120 °C | Operating temperature, min. | -40 °C |
| Operating temperature, max. | 120 °C          |                             |        |

### General information

|                            |      |                            |           |
|----------------------------|------|----------------------------|-----------|
| Halogen                    | No   | Material                   | Polyamide |
| Outer cable diameter, max. | 9 mm | Outer cable diameter, min. | 9 mm      |
| Protection degree          | IP66 | UL 94 flammability rating  | V-0       |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000879    | ETIM 7.0    | EC000879    |
| ETIM 8.0    | EC000879    | ECLASS 9.0  | 27-14-44-21 |
| ECLASS 9.1  | 27-14-44-21 | ECLASS 10.0 | 27-14-44-21 |
| ECLASS 11.0 | 27-14-44-21 | ECLASS 12.0 | 27-14-08-07 |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|                    |   |
|--------------------|---|
| Engineering Data   | <a href="#">CAD data – STEP</a>                   |
| Engineering Data   | <a href="#">EPLAN</a>                             |
| User Documentation | <a href="#">Cabtite Installation Instructions</a> |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>          |