

**CB-VT 200/4,8 WT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

Our self-extinguishing cable ties are suitable for environments with increased fire protection requirements. They comply with EN45545 and are suitable for use in rail vehicles.

**General ordering data**

|            |   |
|------------|---|
| Version    | Cable ties, 4.8 x 200 mm, Polyamide 66, 220 N |
| Order No.  | <a href="#">2659520000</a>                    |
| Type       | CB-VT 200/4,8 WT                              |
| GTIN (EAN) | 4050118682984                                 |
| Qty.       | 100 Stück                                     |

## CB-VT 200/4,8 WT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |        |                 |            |
|------------|--------|-----------------|------------|
| Height     | 200 mm | Height (inches) | 7.874 inch |
| Width      | 4.8 mm | Width (inches)  | 0.189 inch |
| Net weight | 1.4 g  |                 |            |

### Temperatures

|                                  |             |                                  |        |
|----------------------------------|-------------|----------------------------------|--------|
| Operating temperature range      | -40...85 °C | Operating temperature, min.      | -40 °C |
| Operating temperature, max.      | 85 °C       | Continuous operating temp., min. | -40 °C |
| Continuous operating temp., max. | 85 °C       |                                  |        |

### Installation materials

|                                   |       |                                   |              |
|-----------------------------------|-------|-----------------------------------|--------------|
| Bundle diameter, max.             | 50 mm | Bundle diameter, min.             | 3 mm         |
| Cable diameter, max.              | 50 mm | For re-opening                    | No           |
| Halogen                           | No    | Material                          | Polyamide 66 |
| Operating temperature range, max. | 85 °C | Operating temperature range, min. | -40 °C       |
| Tensile strength                  | 220 N | Tensile strength (Pound-force)    | 49 lbf       |
| UL 94 flammability rating         | V-0   | UV-resistant                      | No           |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000046    | ETIM 7.0    | EC000046    |
| ETIM 8.0    | EC000046    | ECLASS 9.0  | 27-14-07-02 |
| ECLASS 9.1  | 27-14-07-02 | ECLASS 10.0 | 27-14-07-02 |
| ECLASS 11.0 | 27-14-07-02 | ECLASS 12.0 | 27-14-07-02 |

### Approvals

Approvals



ROHS Conform

### Downloads

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">EU Declaration of Conformity</a> |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>     |

**Datenblatt**

**CB-VT 200/4,8 WT**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

