

VG 16 HQ K68 4-6.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	Heavy-duty connectors, Accessories, Cable glands, Polycarbonate
Order No.	2715990000
Type	VG 16 HQ K68 4-6.5
GTIN (EAN)	4050118769821
Qty.	1 Stück

Erstellungs-Datum June 5, 2023 10:26:15 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

VG 16 HQ K68 4-6.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 12.2 g

Temperatures

Limit temperature -20 °C ... 100 °C

General information

AF size	27 mm	Cable glands	PG 16
External thread	PG 16	Internal thread	PG 16
Material	Polycarbonate	Protection degree	IP68
Sealing	TPE		

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32	ECLASS 12.0	27-14-08-01

Approvals

ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	Korean Registration of Broadcasting and Communication Equipments
Engineering Data	CAD data – STEP
Product Change Notification	20210205 Technical change to HQ Cable Glands 20210205 Technische Änderung zu HQ Kabelverschraubung
Catalogues	Catalogues in PDF-format