

EPAK-CI-2CO-EP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



The analogue converters of the EPAK series are characterised by their compact design. The wide range of functions available with this series of analogue converters make them suitable for applications which do not require international approvals.

Properties:

- Safe isolation, conversion and monitoring of your analogue signals
- Configuration of the input and output parameters directly on the device via DIP switches
- No international approvals
- High interference resistance

General ordering data

Order No.	7760054309
Type	EPAK-CI-2CO-EP
GTIN (EAN)	6944 169747724
Qty.	1 Stück

Erstellungs-Datum June 1, 2023 10:54:42 AM CEST

EPAK-CI-2CO-EP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 80 g

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-20 °C...60 °C
Operating temperature, min.	-20 °C	Operating temperature, max.	60 °C

Input

Input current	0...20 mA, 4...20 mA	Input resistance, current	≤ 100 Ω
Number of inputs	1		

Output

Load impedance current	≤ 300 Ω	Number of outputs	2
Output current	0...20 mA, 4...20 mA		

Output (analogue)

Output current 0...20 mA, 4...20 mA

General data

Accuracy	0.1% FSR	Configuration	none
Galvanic isolation	between input/output/supply	Power consumption	≤ 1.4 W
Step response time	≤ 500 ms	Temperature coefficient	≤ 300 ppm/K
Voltage supply	20...35 V DC		

Insulation coordination

EMC standards	IEC 61326-1	Galvanic isolation	between input/output/supply
Impulse withstand voltage	3 kV (1.2/50µs)	Insulation voltage	1.5 kV _{eff}
Pollution severity	2	Rated voltage	300 V
Surge voltage category	II		

Connection data

Type of connection	Screw connection	Tightening torque, min.	0.4 Nm
Tightening torque, max.	0.6 Nm	Clamping range, rated connection	2 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	2 mm ²
Wire connection cross section AWG, min.	AWG 30	Wire connection cross section AWG, max.	AWG 14

Classifications

ETIM 6.0	EC002653	ETIM 7.0	EC002653
ETIM 8.0	EC002653	ECLASS 9.0	27-21-01-20
ECLASS 9.1	27-21-01-90	ECLASS 10.0	27-21-01-20
ECLASS 11.0	27-21-01-20	ECLASS 12.0	27-21-01-20

EPAK-CI-2CO-EP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6a722fc5-2d22-41b4-9544-5b95e45a4b77

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Declaration of Conformity
Engineering Data	CAD data – STEP
User Documentation	Instruction sheet
Catalogues	Catalogues in PDF-format

EPAK-CI-2CO-EP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Zeichnungen

