

TS35X7.5 ST POK 1636

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



Similar to illustration

The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

| | |
|------------|---|
| Version | Rail, TS 35, TS 35 x 7.5, Width: 342 mm, without slot, Steel, galvanic zinc plated and passivated |
| Order No. | 8000003910 |
| Type | TS35X7.5 ST POK 1636 |
| GTIN (EAN) | 4050118652703 |
| Qty. | 20 Stück |

TS35X7.5 ST POK 1636

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 7.5 mm | Depth (inches) | 0.295 inch |
| Height | 35 mm | Height (inches) | 1.378 inch |
| Width | 342 mm | Width (inches) | 13.465 inch |
| Net weight | 117.9 g | | |

General information

| | | | |
|--------------------|--------------|------------------|-------------------------------------|
| Integral fixing | Screwed | Material | Steel |
| Material thickness | 1 mm | Stamp dimensions | 6.3 x 20 mm |
| Standards | DIN EN 60715 | Surface finish | galvanic zinc plated and passivated |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001285 | ETIM 7.0 | EC001285 |
| ETIM 8.0 | EC001285 | ECLASS 9.0 | 27-40-06-02 |
| ECLASS 9.1 | 27-40-06-02 | ECLASS 10.0 | 27-40-06-02 |
| ECLASS 11.0 | 27-40-06-02 | ECLASS 12.0 | 27-40-06-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |