

FPL 4G2.5/P/Q4KW/5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Take advantage of our pre-assembled FieldPower® connectors with HQ connectors acc. to IEC 23570 (DESINA) for connecting decentralised motor controller devices quickly and conveniently.

General ordering data

Version	FieldPower®, Cable, Plastic housing, Number of wires: 4, Ölflex Classic 110 4G2.5 or similar, Cross-section: 2.5 mm ² , 5 m
Order No.	8000005229
Type	FPL 4G2.5/P/Q4KW/5
GTIN (EAN)	4032248997541
Qty.	1 Stück

Erstellungs-Datum May 26, 2023 3:27:28 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

FPL 4G2.5/P/Q4KW/5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 1 g

Technical specifications for cable

Bending radius, min., moving	133.5 mm	Bending radius, min., stationary	35,6 mm
Halogen	Yes	Number of wires	4
Temperature range, moving	-5...70 °C	Temperature range, stationary	-40...70 °C

General technical data

Protection degree IP65

Classifications

ETIM 6.0	EC001576	ETIM 7.0	EC001576
ETIM 8.0	EC001576	ECLASS 9.0	27-06-04-02
ECLASS 9.1	27-06-91-90	ECLASS 10.0	27-06-04-02
ECLASS 11.0	27-06-04-02	ECLASS 12.0	27-06-04-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	13ce035c-fa1c-4432-a4df-1b9d07f69a8d

Approvals

Approvals



ROHS Conform

Downloads

Catalogues [Catalogues in PDF-format](#)

FPL 4G2.5/P/Q4KW/5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

