



MCZ SC 0-10V

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Product image



MCZ: The smallest solution

- The smallest analogue signal converter in terminal block format on the market
- Space-saving conversion of analogue signals in the control cabinet thanks to the slim, 6 mm wide module width
- Simple wiring with plug-in cross-connectors

General ordering data

Version	Limit value monitoring, Input : 0-10 V, Output 2 x transistor
Order No.	8260280000
Type	MCZ SC 0-10V
GTIN (EAN)	4008 190985417
Qty.	10 Stück

Erstellungs-Datum May 26, 2023 3:40:02 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

MCZ SC 0-10V

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	63.2 mm	Depth (inches)	2.488 inch
Width	6 mm	Width (inches)	0.236 inch
Length	91 mm	Length (inches)	3.583 inch
Net weight	29.6 g		

Temperatures

Storage temperature	-25 °C...60 °C	Operating temperature	0 °C...50 °C
Operating temperature, min.	0 °C	Operating temperature, max.	50 °C
Humidity	40 °C / 93 % rel. humidity, no condensation		

Probability of failure

SIL in compliance with IEC 61508	None		
----------------------------------	------	--	--

Input

Input resistance, voltage	60 kΩ	Input voltage	0...10 V
Number of inputs	1		

Output

Cut-off frequency (-3 dB)	100 Hz	Number of outputs	2
---------------------------	--------	-------------------	---

General data

Configuration	Potentiometer	Current consumption	15 mA
Galvanic isolation	Without isolation	Rail	TS 35
Step response time	< 250 μs (switching threshold at 90% of max. input signal; R _i ≤ 1 kΩ)	Temperature coefficient	max. 250 ppm/K
Voltage supply	24 V DC ± 20 %		

Insulation coordination

EMC standards	EN 55011, EN 61000-6	Galvanic isolation	Without isolation
Insulation voltage input or output/rail	4 kV _{eff} / 1 min.		

Connection data

Type of connection	Tension-clamp connection	Clamping range, rated connection	1.5 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	1.5 mm ²

Classifications

ETIM 6.0	EC002654	ETIM 7.0	EC002654
ETIM 8.0	EC002654	ECLASS 9.0	27-21-01-22
ECLASS 9.1	27-21-01-22	ECLASS 10.0	27-21-01-22
ECLASS 11.0	27-21-01-22	ECLASS 12.0	27-21-01-22

MCZ SC 0-10V

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Tender specification sheets

Long specification

Short specification

Trip amplifier for monitoring a 0...10 V standard signal with two switching outputs
Trip amplifier in 6 mm width for analogue 0...10 V standard signals with two PNP-transistor switch outputs for monitoring an upper and lower threshold (adjustable via potentiometer). DIP switches can be used to select a range of 300 mV to 10 V, 30 mV to 1 V, and 10 mV to 100 mV on the input side.

Add-on housing for TS35 rail mounting
Dimensions: L/W/H 91/6/ 63.2 mm
Tension-clamp connection / Nominal cross-section 1.5 mm²
Protection degree: IP 20

Input
0...10 V

ranges 300 mV... 10 V / 30 mV... 1 V / 10 mV... 100 mV

Output
Double switching output PNP/ 50 mA per channel

adjustable via potentiometer
Switching hysteresis 1 % of input
Step response time < 250 us (10...90 %)

Temperature coefficient < 250 ppm K
Auxiliary power 24 V DC +/- 20 %
Ambient temperature range 0°C...+50 °C

Isolation 1.5 kV
Approvals cURus, CSA

Type
MCZ SC 0-10V

Trip amplifier for monitoring a 0...10 V standard signal with two switching outputs
Trip amplifier in 6 mm width for analogue 0...10 V standard signals with two PNP-transistor switch outputs for monitoring an upper and lower threshold (adjustable via potentiometer). DIP switches can be used to select a range of 300 mV to 10 V, 30 mV to 1 V, and 10 mV to 100 mV on the input side.

Erstellungs-Datum May 26, 2023 3:40:02 PM CEST

MCZ SC 0-10V

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	35d83707-6a3b-45b5-b9f8-6ba8184c863e

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E141197

Downloads

Approval/Certificate/Document of Conformity	Declaration of Conformity
Engineering Data	CAD data – STEP
Engineering Data	WSCAD, EPLAN
User Documentation	Instruction sheet
Catalogues	Catalogues in PDF-format
Brochures	



MCZ SC 0-10V

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

Connection diagram



dimensions

