

CB 160/2,6 NC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

General ordering data

Version	Cable ties, 2.6 x 160 mm, Polyamide 66, 80 N
Order No.	7940006048
Type	CB 160/2,6 NC
GTIN (EAN)	4032248520121
Qty.	100 Stück

Erstellungs-Datum June 1, 2023 11:25:11 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

CB 160/2,6 NC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	1 mm	Depth (inches)	0.039 inch
Height	160 mm	Height (inches)	6.299 inch
Width	2.6 mm	Width (inches)	0.102 inch
Net weight	0.46 g		

Temperatures

Operating temperature range	-40...85 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	85 °C		

Installation materials

Bundle diameter, max.	40 mm	Bundle diameter, min.	1 mm
Cable diameter, max.	40 mm	For re-opening	No
Halogen	No	Material	Polyamide 66
Operating temperature range, max.	85 °C	Operating temperature range, min.	-40 °C
Tensile strength	80 N	Tensile strength (Pound-force)	18 lbf
UL 94 flammability rating	V-2	UV-resistant	No

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02	ECLASS 12.0	27-14-07-02

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E317499

Downloads

Approval/Certificate/Document of Conformity	DE PI830000 160627 001
Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format

Datenblatt

CB 160/2,6 NC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

