

DI350/4-20MA/0-100.0/24VDC/X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Do not use product for new
 developments



Devices in this series display universal analogue process values.

Depending on the version, the devices convert/isolate the signals into an analogue current signal and have additional limit value relays which switch further signals.

Features:

- Several sensor variants can be processed.
- An auxiliary power supply is required.
- Even in unfavourable lighting conditions, the display value is clearly visible.

General ordering data

Version	Signal converter/insulator, 4...20 mA
Order No.	7940010185
Type	DI350/4-20MA/0-100.0/24VDC/X
GTIN (EAN)	4032248564316
Qty.	1 Stück
Delivery status	This article will no longer be available in the future.

Erstellungs-Datum May 26, 2023 3:17:45 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

DI350/4-20MA/0-100.0/24VDC/X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Height	48.8 mm	Height (inches)	1.921 inch
Width	96.6 mm	Width (inches)	3.803 inch
Length	137 mm	Length (inches)	5.394 inch
Net weight	339 g		

Temperatures

Storage temperature	-25 °C...70 °C	Operating temperature	0 °C...60 °C
Operating temperature, min.	0 °C	Operating temperature, max.	60 °C
Humidity	0...90 % (no condensation)		

Display

Display range	-1999...1999	Display value	Percentage or real value display
Format	1-line / decimal point: 1.000, 100.0, 10.00	Type	3.5 digits, red LED, 14.2 mm

General data

Input/Output	Voltage/current input	Linearity	< 0.1 % typ.
Long-term drift	0.1 % / 10.000 h	Power consumption	6 W @ 24 V DC
Step response time	200 ms (10...90 %)	Temperature coefficient	≤ 0.02 % / °C
Type of connection	Screw connection	Voltage supply	24 V DC (12...35 V DC)

Input

Input resistance	22 Ω	Input signal	4...20 mA
Supply voltage (loop-powered mode)	24 V DC (up to 25 mA)	Type	Analogue current signals

Loop powered mode

Supply voltage (loop-powered mode)	24 V DC (up to 25 mA)
------------------------------------	-----------------------

Insulation coordination

EMC standards	DIN EN 61326	Impulse withstand voltage	4 kV (1.2/50 μs)
Insulation voltage	1 kV input / power supply		

Connection data

Type of connection	Screw connection	Clamping range, rated connection	1.5 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	2.5 mm ²

Classifications

ETIM 6.0	EC000677	ETIM 7.0	EC000677
ETIM 8.0	EC000677	ECLASS 9.0	27-14-31-10
ECLASS 9.1	27-21-03-01	ECLASS 10.0	27-14-31-10
ECLASS 11.0	27-14-31-10	ECLASS 12.0	27-14-31-10

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Erstellungs-Datum May 26, 2023 3:17:45 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

DI350/4-20MA/0-100.0/24VDC/X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E256486
Certificate no. (cULusEX)	E338066

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	

DI350/4-20MA/0-100.0/24VDC/X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

Electric symbol

