

VSPC BASE 2SL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Base element for the pluggable VSPC arrester, integrated PE foot in impedance-neutral VSPC BASE. Can safely discharge up to 20 kA (8/20 μ s) and 2.5 kA (10/350 μ s) to the PE.

General ordering data

| | |
|------------|---|
| Version | Surge protection, Flange-mounted housing, Flange-mounted housing |
| Order No. | 8924720000 |
| Type | VSPC BASE 2SL |
| GTIN (EAN) | 4032248696369 |
| Qty. | 1 pc(s). |

Creation date March 2, 2023 11:11:29 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

VSPC BASE 2SL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 69 mm | Depth (inches) | 2.717 inch |
| Height | 90 mm | Height (inches) | 3.543 inch |
| Width | 17.8 mm | Width (inches) | 0.701 inch |
| Net weight | 65 g | | |

Temperatures

| | | | |
|-----------------------------|----------------|-----------------------------|----------------|
| Storage temperature | -40 °C...80 °C | Operating temperature | -40 °C...70 °C |
| Operating temperature, min. | -40 °C | Operating temperature, max. | 70 °C |
| Humidity | 5...96 % | | |

Rated data UL

| | | | |
|----------------------|---------|----------------|---------------------|
| Certificate No. (UL) | E311081 | UL certificate | UL 497b Certificate |
|----------------------|---------|----------------|---------------------|

CSA protection data

| | | | |
|--|------|------------------------------------|--------|
| Gas group C | IIB | Gas group D | IIA |
| Gas groups A, B | IIC | Input current, max. I _I | 300 mA |
| Internal inductance, max. L _I | 0 µH | | |

General data

| | | | |
|---------------------------|--------------------|-------------------|---------------------------------------|
| Colour | black | Design | Terminal, miscellaneous |
| Optical function display | No | Protection degree | IP20 |
| Rail | TS 35, TS 35 x 7.5 | Segment | Measurement - Monitoring - Setting |
| UL 94 flammability rating | V-0 | Version | Flange-mounted housing |

Insulation coordination acc. to EN 50178

| | | | |
|--------------------|---|------------------------|-----|
| Pollution severity | 2 | Surge voltage category | III |
|--------------------|---|------------------------|-----|

Rated data IEC / EN

| | | | |
|------------------------------|--|--------------------|-------|
| Rated current I _N | 300 mA | Signalling contact | No |
| Standards | IEC 61643-21, IEC 62305, DIN EN 60079-0:2009, DIN EN 60079-11:2007, DIN EN 60079-26:2007, DIN EN 61241-11:2006 | Voltage type | AC/DC |

Further details of approvals

| | |
|------------------|-----------------|
| GOST certificate | GOST-Zertifikat |
|------------------|-----------------|

VSPC BASE 2SL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Connection data

| | | | |
|--|---------------------|--|---------------------|
| Stripping length | 7 mm | Type of connection | Screw connection |
| Stripping length, rated connection | 7 mm | Tightening torque, min. | 0.5 Nm |
| Tightening torque, max. | 0.8 Nm | Clamping range, min. | 0.5 mm ² |
| Clamping range, max. | 4 mm ² | Wire cross-section, solid, min. | 0.5 mm ² |
| Wire cross-section, solid, max. | 4 mm ² | Wire connection cross section, finely stranded, max. | 2.5 mm ² |
| Conductor cross-section, flexible, AEH (DIN 46228-1), min. | 0.5 mm ² | Conductor cross-section, flexible, AEH (DIN 46228-1), max. | 2.5 mm ² |
| Connection cross-section, stranded, min. | 0.5 mm ² | Connection cross-section, stranded, max. | 2.5 mm ² |
| Blade size | 0.6 x 3.5 mm | | |

Ratings IECEx/ATEX/cUL

| | |
|-----------------|-----------------|
| cUL certificate | cUL Certificate |
|-----------------|-----------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000472 | ETIM 7.0 | EC000472 |
| ETIM 8.0 | EC000472 | ECLASS 9.0 | 27-13-08-03 |
| ECLASS 9.1 | 27-13-08-07 | ECLASS 10.0 | 27-13-08-03 |
| ECLASS 11.0 | 27-13-08-03 | ECLASS 12.0 | 27-17-15-91 |

Tender specification sheets

| | | | |
|--------------------|---|---------------------|---|
| Long specification | <p>Base element can take a protected plug for up to two floating-ground powered paired cables. When the base unit is fitted, a simultaneous electrically conducting contact is made between the mounting rail (earth) and the reference potential (ground) of the protection circuit in the plug. Mechanical coding of the base element to the protected plug according to switching type and rated voltage. The base unit is coded itself by the first insertion of a protected plug. Possible to mark all terminals</p> | Short specification | <p>Base element receives a protected plug for two floating-ground powered paired cables with direct earthing.</p> |
|--------------------|---|---------------------|---|

Approvals

Approvals



| | |
|-----------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UL) | E311081 |

Creation date March 2, 2023 11:11:29 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

3

VSPC BASE 2SL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Downloads**

| | |
|---|--|
| Approval/Certificate/Document of Conformity | SIL Paper EU Konformitätserklärung / EU Declaration of Conformity |
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, Zuken E3.S |
| User Documentation | Beipackzettel / Instruction sheet |
| Catalogues | Catalogues in PDF-format |
| Brochures | |


VSPC BASE 2SL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Drawings

Electric symbol



Circuit diagram

| Category | Testing pulse | Surge voltage | Surge current | Pulse | Type |
|----------|-------------------|---------------------------------|----------------------------------|-------|---|
| C1 | Quick-rising edge | 0.5 - 2 kV with 1.2/50 µs | 0.25 - 1 kA mit 8/20 µs | 300 | Surge voltage arrester |
| C2 | Quick-rising edge | 2 - 10 kV with 1.2/50 µs | 1 - 5 kA mit 8/20 µs | 10 | Surge voltage arrester |
| C3 | Quick-rising edge | ≥ 1 kV with 1 kV/µs | 10 - 100 A mit 10/10000 µs | 300 | Surge voltage arrester |
| D1 | High power | ≥ 1 kV | 0.5 - 2.5 kA mit 10/350 µs | 2 | Arrester for lightning current and surge voltages |

Discharge capacity