


DK F-U DK5 0-16KHZ 24V

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration

Product is no longer available, Data sheet for information only



MCZ: The smallest solution

- The smallest analogue signal converter in terminal block format on the market
- Space-saving conversion of analogue signals in the control cabinet thanks to the slim, 6 mm wide module width
- Simple wiring with plug-in cross-connectors

General ordering data

Version	Frequency signal converter, Input : Frequency, 0...50/ 100/ 500 Hz; 0...1/ 5/ 10/ 16 kHz, Output : 0-10 V
Order No.	8283810001
Type	DK F-U DK5 0-16KHZ 24V
GTIN (EAN)	4008190371074
Qty.	10 Stück

Erstellungs-Datum May 26, 2023 3:40:11 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

DK F-U DK5 0-16KHZ 24V

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Height	64 mm	Height (inches)	2.52 inch
Width	12 mm	Width (inches)	0.472 inch
Length	76.8 mm	Length (inches)	3.024 inch
Net weight	22.9 g		

Temperatures

Storage temperature	-25 °C...60 °C	Operating temperature	0 °C...50 °C
Operating temperature, min.	0 °C	Operating temperature, max.	50 °C

Input

Input frequency	0...50/ 100/ 500 Hz; 0...1/ 5/ 10/ 16 kHz	Input resistance, voltage	10 kΩ
Number of inputs	1		

Output

Number of outputs	1	Output voltage, note	0(2)...10 V
-------------------	---	----------------------	-------------

General data

Accuracy	0.5 % (8-bit resolution)	Current consumption	32 mA + I-Last
Galvanic isolation	2-way isolator	Input/Output	f/ DC
Rail	TS 35, TS 32	Voltage supply	24 V DC ± 10 %

Insulation coordination

Galvanic isolation	2-way isolator	Insulation voltage	2.5 kV
Insulation voltage input or output/rail	4 kV _{eff}		

Connection data

Type of connection	Screw connection	Clamping range, rated connection	4 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	4 mm ²

Classifications

ETIM 6.0	EC002918	ETIM 7.0	EC002918
ETIM 8.0	EC002918	ECLASS 9.0	27-21-01-28
ECLASS 9.1	27-21-01-28	ECLASS 10.0	27-21-01-28
ECLASS 11.0	27-21-01-28	ECLASS 12.0	27-21-01-28

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	35d83707-6a3b-45b5-b9f8-6ba8184c863e

DK F-U DK5 0-16KHZ 24V

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of
Conformity

[Declaration of Conformity](#)

Catalogues

[Catalogues in PDF-format](#)