

H4,0/20DS GR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- Polypropylene conical cable entry funnel
 - Heat-resistant up to 105°C
- For conductors from 0.5 – 10.0 mm² (AWG 20-7)
Material: E-Cu, tin galvanised
Dimensional tolerance acc. to DIN 46228 sect. 4

General ordering data

| | |
|------------|--|
| Version | Wire-end ferrule, Standard, 15 mm, 12 mm, grey |
| Order No. | 9203630000 |
| Type | H4,0/20DS GR |
| GTIN (EAN) | 4032248565078 |
| Qty. | 500 pc(s). |
| Packaging | loose |

Creation date February 28, 2023 9:50:48 AM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

H4,0/20DS GR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | |
|------------|--------|
| Net weight | 0.26 g |
|------------|--------|

Technical data

| | | | |
|------------------------|--|---------|----------|
| Description of article | Wire end ferrule with plastic collar, special size, grey | Version | Standard |
|------------------------|--|---------|----------|

Wire-end ferrules

| | | | |
|-----------------------------|-------------------|---|---------------|
| Collar diameter (D2) | 4.7 mm | Colour code | Miscellaneous |
| Conductor cross-section | 4 mm ² | Contact surface diameter (D1) | 2.9 mm |
| Contact surface length (L2) | 12 mm | L1 in mm | 20 mm |
| Metal sleeve thickness (S1) | 0.2 mm | Plastic collar thickness (S2) | 0.5 mm |
| Stripping length | 15 mm | Wire connection cross section AWG, max. | AWG 12 |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000005 | ETIM 7.0 | EC000005 |
| ETIM 8.0 | EC000005 | ECLASS 9.0 | 27-40-02-01 |
| ECLASS 9.1 | 27-40-02-01 | ECLASS 10.0 | 27-40-02-01 |
| ECLASS 11.0 | 27-40-02-01 | ECLASS 12.0 | 27-40-02-01 |

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|--|
| Engineering Data | WSCAD |
| User Documentation | Technical information - EN Technical information - DE |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

Data sheet

H4,0/20DS GR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

