

MULTIMETER 1037**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Multimeters are capable of measuring a number of variables. Each instrument can measure voltage and resistance, as well as performing continuity and diode testing as standard.

In addition, the individual multimeters also feature extra measuring options such as current, frequency, capacitance and temperature. Digital multimeters have the advantage of a clear display which can be read easily and directly. With these instruments, mistakes arising from faulty conversion of the measuring ranges or misreading the display are a thing of the past.

General ordering data

Version	Testing tools, Multimeter
Order No.	9423580000
Type	MULTIMETER 1037
GTIN (EAN)	4032248406142
Qty.	1 Stück

MULTIMETER 1037

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	66 mm	Depth (inches)	2.598 inch
Height	44 mm	Height (inches)	1.732 inch
Width	214.5 mm	Width (inches)	8.445 inch
Net weight	880 g		

Technical data

Description of article	Digital multimeter	Version	Multimeter + clamp-on meter
------------------------	--------------------	---------	-----------------------------

Measuring and testing devices

AC voltage measuring range	0.2 - 750 V	Battery type	9V block battery
DC voltage measuring range	0.2 - 1000 V	Display	digital
Frequency measurement	No	Frequency range, max.	500 Hz
Frequency range, min.	50 Hz	Measured capacitance value, max.	200 µF
Measured current value, max.	200 A	Measuring range category	CAT III
Opening width of current-measuring clamp-on attachment	23 mm	Resistance measuring range, max.	200 kΩ
Resistance measuring range, min.	0.2 Ω	Selection of measuring range	Manual
Test probe	Yes	Tested and approved according to	EN/IEC 61010-1
Working temperature, max.	50 °C	Working temperature, min.	0 °C

Classifications

ETIM 6.0	EC000069	ETIM 7.0	EC000069
ETIM 8.0	EC000069	ECLASS 9.0	27-20-03-01
ECLASS 9.1	27-20-03-08	ECLASS 10.0	27-20-03-01
ECLASS 11.0	27-20-03-01	ECLASS 12.0	27-20-03-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	

MULTIMETER 1037

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Zeichnungen

Example of use

